



# MAINTENANCE CART MODEL MC1

INDUSTRIAL TOOL STORAGE  
MADE IN THE HEART OF THE U.K.

7158440


To be professional in maintenance you require:

- All your tools with you.
- To find fittings & fasteners easily.
- To have a work station.

## THE ANSWER.....A MOBILE MAINTENANCE CART

Compact for ease  
of movement

Heavy duty  
for durability



Available in green or red

- The five drawers measure 19 $\frac{3}{8}$ " (492mm) W x 13" (330mm) D  
Two drawers are 2 $\frac{1}{16}$ " (68mm) H, two are 3 $\frac{1}{16}$ " (93mm) H and one is 4 $\frac{1}{16}$ " (119mm) H.
- Top till is 1 $\frac{3}{4}$ " (44mm) H.
- Castors are 4" dia. x 1 $\frac{1}{4}$ ".
- Overall size: 23 $\frac{1}{2}$ " (596mm) W x 15" (381mm) D x 30 $\frac{3}{8}$ " (784mm) H.
- Weight: 71.2 lbs. (32.3 kgs.) packed.

Your Local Distributor:

# STANDARD INDUSTRIAL RANGE

## 6 DRAWER ROLLER CABINET MODEL 2706

- All drawers measure 22 $\frac{3}{8}$ " (568mm) W x 16 $\frac{1}{2}$ " (419mm) D.  
Two drawers are 2" (50mm) H, two are 3 $\frac{1}{4}$ " (95mm) H and two are 6 $\frac{3}{4}$ " (171mm) H.
- Overall size:  
26 $\frac{5}{8}$ " (676mm) W x 17 $\frac{7}{8}$ " (454mm) D x 30" (762mm) H.
- Weight: 114.4 lbs. (52 kgs.)



7158233

*H = 902mm including casters*

## 3 DRAWER ROLLER CABINET MODEL 2713 With Base Compartment


- All drawers measure 22 $\frac{3}{8}$ " (568mm) W x 16 $\frac{1}{2}$ " (419mm) D.  
Two drawers are 3 $\frac{1}{4}$ " (95mm) H and one is 4 $\frac{7}{8}$ " (123mm) H.  
Lower storage compartment measures 23 $\frac{1}{2}$ " (596mm) W x 16 $\frac{3}{4}$ " (425mm) D x 10 $\frac{3}{4}$ " (273mm) H.
- Overall size:  
26 $\frac{5}{8}$ " (676mm) W x 17 $\frac{7}{8}$ " (454mm) D x 30" (762mm) H.
- Weight: 91 lbs. (41.4 kgs.)



7158245

## 6 DRAWER ROLLER CABINET MODEL 2716 With Base Compartment

- All drawers measure 22 $\frac{3}{8}$ " (568mm) W x 16 $\frac{1}{2}$ " (419mm) D.  
Three drawers are 2" (50mm) H, two are 3 $\frac{1}{4}$ " (95mm) H and one is 4 $\frac{7}{8}$ " (123mm) H.  
Lower storage compartment measures 23 $\frac{1}{2}$ " (596mm) W x 16 $\frac{3}{4}$ " (425mm) D x 10 $\frac{3}{4}$ " (273mm) H.
- Overall size:  
26 $\frac{5}{8}$ " (676mm) W x 17 $\frac{7}{8}$ " (454mm) D x 37" (939mm) H.
- Weight: 124.5 lbs. (56.6 kgs.)



**SOME SUGGESTED  
COMBINATIONS**