



Identification ties and plates for marking cable bundles

IT-Ties


One of the major benefits is the ability to both secure and identify cable bundles at different times.

Features and Benefits


- Identification ties made of Polyamide 6.6
- For simple identification and securing of cable bundles in one step
- Printable labels are available for a professional finish
- Manual or temporary marking is possible with an indelible pen (T82S-BK / T82R-RD)



One operation with two benefits.




IT18FL



IT18R

MATERIAL	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C
Flammability	UL94 V2
Specifications	Cage Code 53421, DNV GL, MS3368, SAE - AS33681, UL-ZODZ2.E64139




TYPE	Bundle Ø min.	Bundle Ø max.	Width (W)	Height (H)	Length (L)	Width (W2)	 N	Recommended Labels	Pack Cont.	Colour	Article-No.
IT18FL	1.5	19.0	20.5	9.0	110.0	2.5	80	TAG18-07TD1	100 pcs.	Natural (NA)	111-81919
IT18R	6.0	22.0	25.0	8.0	100.0	2.3	80	TAG23-06TD1	100 pcs.	Natural (NA)	111-81821

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.


 N = Minimum Loop Tensile Strength for Cable Ties (Newton)






Identification ties and plates for marking cable bundles


IT-Ties




IT50R



IT50RD



IT50RT



IT50L

TYPE	Bundle Ø min.	Bundle Ø max.	Width (W)	Height (H)	Length (L)	Width (W2)		Recommended Labels	Pack Cont.	Colour	Article-No.
IT50R	9.5	44.5	28.0	12.9	203.0	4.6	225	TAG23-10TD1	100 pcs.	Natural (NA)	111-85019
IT50RD	10.0	44.0	29.0	26.3	205.0	4.7	225	TAG26-21TD1	50 pcs.	Natural (NA)	111-85219
IT50RT	10.0	44.0	46.0	26.3	205.0	4.7	225	TAG43-21TD1	50 pcs.	Natural (NA)	111-85119
IT50L	19.0	100.0	56.0	12.8	390.0	4.7	225	TAG52-10TD1	100 pcs.	Natural (NA)	111-85319

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

TYPE	Description	Colour	Pack Cont.	Article-No.
T82S-BK	Indelible Marker Pen	Black (BK)	2 pcs.	500-50820
T82R-RD	Indelible Marker Pen	Red (RD)	2 pcs.	500-50822

Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.