

FRAME SHELF



APPLICATION

The PROLINE G2 Frame Shelf mounts to the vertical hole pattern on a frame and provides a stationary surface for equipment.

SPECIFICATIONS

- 16-gauge (1.5 mm) steel

FINISH

- Painted polyester powder paint; RAL 7035 Light Gray
- Custom colors available

LOAD RATING


- 400 lb. (181 kg)

BULLETIN: P40

Catalog Number	Width (mm)	Width (in.)	Depth (mm)	Depth (in.)	Fits Frame Width x Depth mm
P2ASHF45	348	13.7	407	16.0	400x500
P2ASHF46	348	13.7	507	20.0	400x600
P2ASHF64	548	21.6	307	16.0	600x400
P2ASHF65	548	21.6	407	16.0	600x500
P2ASHF66	548	21.6	507	20.0	600x600
P2ASHF68	548	21.6	707	27.8	600x800
P2ASHF84	748	29.4	307	16.0	800x400
P2ASHF85	748	29.4	407	16.0	800x500
P2ASHF86	748	29.4	507	20.0	800x600
P2ASHF88	748	29.4	707	27.8	800x800
P2ASHF810	748	29.4	907	25.7	800x1000
P2ASHF104	948	37.3	307	16.0	1000x400
P2ASHF105	948	37.3	407	16.0	1000x500
P2ASHF106	948	37.3	507	20.0	1000x600
P2ASHF108	948	37.3	707	27.8	1000x800

WxD dimensions are in mm.

FRAME PULL-OUT SHELF



APPLICATION

PROLINE G2 Frame Pull-Out Shelf allows easy access to shelf-mounted devices.

SPECIFICATIONS

- Mounts to the front and rear frame uprights
- The shelf is 16-gauge (1.5-mm) steel with 12-gauge (2.5-mm) steel supports

FINISH

- Painted polyester powder paint; RAL 7035 Light Gray
- Custom colors available

LOAD RATING

110 lb. (50 kg)

BULLETIN: P40

Catalog Number	Fits Frame Width mm	Width mm/in.	Depth mm/in.	Pull-Out mm/in.
P2ASHFP6	600	557 21.9	505 19.9	450 17.7
P2ASHFP8	800	757 29.8	505 19.9	450 17.7
P2ASHFP6EXT	600	557 21.9	705 27.8	670 26.4
P2ASHFP8EXT	800	757 29.8	705 27.8	670 26.4

FRAME PRINTER SHELF



APPLICATION

The PROLINE G2 Frame Printer Shelf mounts directly to a modular frame and can be used for supporting a continuous feed printer or other applications where multiple pull-out shelves are desired.

SPECIFICATIONS

- Lower shelves are vertically adjustable
- The entire unit slides out 17 in. (431 mm) from the enclosure, allowing easy accessibility
- Fits 600- or 800-mm wide frames that are 600 mm deep or greater

FINISH

- Painted polyester powder paint; RAL 7035 Light Gray
- Custom colors available

BULLETIN: P40

Catalog Number	Width mm/in.	Depth mm/in.	Fits Frame Width mm
P2ASHP6	547 21.6	506 19.9	600
P2ASHP8	747 29.4	506 19.9	800

Frame Width dimensions are in mm.

Notes