








The Sound of Innovation

Main Menu

click on category links

	Studio Bundles	4
	Absorption Panels	5
	Bass Traps	6
	Foam Edging	6
	Ultimate Isolators	6
	Diffusors	7
	Mounting Options	7

Professional Studio Bundles



Studio Bundles

UA-KIT-SB1, 17800

12" x 12" x 2" Wedge-style Professional Acoustic Wall Panels – QTY 18

Specs:

- 18 traditional wedge-style acoustic panels
- Professional panels for absorption
- Reduce unwanted room reverberation
- Apply to walls in variety of patterns
- Adhesive tape included
(Placement ONLY, not permanent)



UA-KIT-SB2, 17801

12" x 12" x 2" Bevel & Wedge Style Professional Acoustic Panels – QTY 24 Mix

Specs:

- 12 elegant bevel acoustic panels combined with 12 traditional acoustic panels in one kit
- Professional panels for absorption
- Reduce unwanted room reverberation
- Apply to walls in variety of patterns
- Adhesive tape included
(Placement ONLY, not permanent)



UA-KIT-SB3, 17802

12" x 12" x 2" Bevel and Bevel with Vinyl Acoustic Wall Panels and Bass Traps with Vinyl - QTY 26 Mix

Specs:

- 12 elegant bevel-style acoustic panels
- 12 bevel panels with perforated vinyl layers that enhances performance in lower frequencies
- Two bass traps with vinyl layer
- Adhesive tape included
(Placement ONLY, not permanent)



Professional Absorption Panels



Hex Series Absorption Panels

Designed for users looking to treat unique problems in the listening room, as well as to lend a personal touch to any creative space- the new Hex Series absorption panels from Ultimate Acoustics offer a stylish and affordable option for your problem solving. Available in 2 packs of 12" or 24", the panels come in a standard charcoal colored foam only design, or with our enhanced, perforated vinyl covering, which allows you to choose from a variety of colors.

24" Hexagonal Foam Wall Panel

- UA-HX-24CH, 17826 (Charcoal)
- UA-HX-24BL, 17829 (Charcoal w/Blue Vinyl)
- UA-HX-24BR, 17828 (Charcoal w/Brown Vinyl)
- UA-HX-24BK, 17827 (Charcoal w/Black Vinyl)
- UA-HX-24OR, 17831 (Charcoal w/Orange Vinyl)
- UA-HX-24GR, 17832 (Charcoal w/Gray Vinyl)
- UA-HX-24KW, 17830 (Charcoal w/Butterscotch Vinyl)
- Design Style: Hexagon
- Type: Absorption
- Size: 24" x 20.75"
- QTY: 2 Pack



12" Hexagonal Foam Wall Panel

- UA-HX-12CH, 17819 (Charcoal)
- UA-HX-12BL, 17822 (Charcoal w/Blue Vinyl)
- UA-HX-12BK, 17820 (Charcoal w/Black Vinyl)
- UA-HX-12OR, 17824 (Charcoal w/Orange Vinyl)
- UA-HX-12GR, 17825 (Charcoal w/Gray Vinyl)
- UA-HX-12BR, 17821 (Charcoal w/Brown Vinyl)
- UA-HX-12KW, 17823 (Charcoal w/Butterscotch Vinyl)
- Design Style: Hexagon
- Type: Absorption
- Size: 12" x 10.375"
- QTY: 2 Pack



Professional Absorption Panels




Bevel-Style with Vinyl Layer

Bevel-Style Absorption Panel Professional Studio Foam with Vinyl Layer

Specs:

- Two bevel-style acoustic panels
- Perforated vinyl layer enhances performance in lower frequencies
- Adhesive tape included
(Placement ONLY, not permanent)




Bevel-Style

Bevel-Style Absorption Panel Professional Studio Foam

Specs:

- Traditional bevel - style acoustic panels
- Reduce unwanted room reverberation
- Adhesive tape included
(Placement ONLY, not permanent)



Wedge-Style

Wedge-Style Absorption Professional Studio Foam

Specs:

- Two Wedge-style acoustic panels
- Reduce unwanted room reverberation
- Adhesive tape included
(Placement ONLY, not permanent)



Professional Bass Traps, Foam Edging & Ultimate Isolators



Bevel-Style with Vinyl Layer

UA-BTBV, 17607

Two Professional Acoustic Bass Traps, Bevel Design with Vinyl

Specs:

- Controls low-frequency room nodes that gather in 90-degree angled spaces (the corners of your room)
- Perforated vinyl layer enhances performance in lower frequencies
- Adhesive tape included for installation assistance (adhesive spray recommended)
- Two pack



Bevel-Style

UA-BTB, 17615

Two Professional Acoustic Bass Traps, Bevel Design

Specs:

- Controls low-frequency room nodes that gather in 90-degree angled spaces (the corners of your room)
- Adhesive tape included for installation assistance (adhesive spray recommended)
- Two pack



Acoustic Foam Edging

UA-FE-2, 17629

Acoustic Foam Edging – 2" x 2" x 24"

Specs:

- Professional 2" x 2" x 24" acoustic foam edging
- Solid foam base for maximum absorption
- Design Style: Prism
- Sold in units of four



Ultimate Isolator

UA-ISO-100, 17807 (36 Pack) / 17808 (9 Pack)
Ultimate Isolator™ Pads For Studio Monitor
(Sold In Pairs)

Specs:

- Increase Clarity
- Unique notched design locks wedges together regardless of angle!
- Configurations: 5 (Angled up at 4° or 8°, Angled down at 4° or 8°, and Flat 0°)
- Size: 12" long x 4" wide x 2" tall
- Weight Limitations: 100 lbs.
- Sold in Pairs



Complete Set

Professional Diffusors and Mounting Options



Stepped Diffusors

Stepped Diffusors help maintain a “live” sound and lend a sense of dimension to any room. The Stepped Diffusors come in either a white or black textured finish.

Specs:

- Size: 24" x 18"
- Type: Diffusor
- Quantity: Four
- Design Style: Rectangled/Stepped
- Colors: Black & White



Pyramid Diffusors

Pyramid Diffusors help maintain a “live” sound and lend a sense of dimension to any room. The Pyramid Diffusors come in either a white or black textured finish.

Specs:

- Size: 24" x 24"
- Type: Diffusor
- Quantity: Four
- Design Style: Pyramid
- Colors: Black & White



Mounting Options

UA-AS1, 17818 Acoustic Adhesive Spray

Specs:

- Size: 12" x 12" x 2"
- Net Wt. 13 OZ. (369 g)
- Web Spray Nozzle



..... The Sound of Innovation