Specifications LW341H (EU/CIS)

Specifical	LIUIIS				LVV34111(LO/CI.
			32	43	49
DISPLAY	Туре			Slim Direct	
	Resolution		1,920 x 1,080 (FHD)		
	Brightness		300cd/m <sup>2</sup>		
	Dynamic Contrast Ratio		1,000,000:1		
	Static Contrast Ratio		1,200:1		
	Viewing Angle Degree		178° / 178°		
BROADCASTING SYSTEM	Analog		PAL/SECAM		
	Digital		DVB-T2/C/S2		
VIDEO	Triple XD Engine		•		
	Real Cinema 24p (3:3 Pull down)				
	Aspect Ratio		8 modes (16:9, Just Scan, Original, Full Wide, 4:3, 14:9, Cinema Zoom 1, Zoom)		
AUDIO	Audio Output / Speaker System		10W + 10W / 2.0 ch		
	Sound Mode		6 modes (Standard, News, Music, Cinema, Sport, Game)		
	Clear Voice		•		
GENERAL FEATURES		Туре	Pro:Centric V		
	Pro:Centric®	Pro:Centric Application	PCA 3.7 or below		
		RF	1 Tuner		
		HCAP (SDK)	GEM / Flash		
	Management Management				
			Diagnostics (USB)		
	Interactivity		HTNG / HDMI-CEC		
	Connectivity		MHL		
	RJP Compatibility		LG / Teleadapt (RS-232C), Teleadapt / Guestlink (HDMI CEC)		
	Advanced Setting Option		Auto Off / Auto Sleep, Smart Energy Saving, Motion Eye Care		
	Anti-theft System		Kensington Lock, Credenza / Security Screw Hole, Lock Down Plate, Commercial Swivel Stand		
COMMERCIAL FEATURES		Welcome Screen/Video, One Channel Map, Hotel Mode, Lock Mode, IR Out, Multi IR Code, External Speaker Out, SNMP, USB Cloning, USB Auto Playback, Time Scheduler			
INTERFACE	Side		HDMI In, USB 2.0, CI Slot		
	Rear		RF In (2), Component In (Video, RCA5), Component In (Audio), Optical Audio Out, HDMI / HDCP Input, RS-232C, Headphone Out, RGB In, PC Audio Input, LAN Port (MHEG / SERVICE), External Speaker Out		
CABINET (Unit : mm)	Bezel Width (L/R, U, B) : on bezel based		14.1, 13.6, 19.1	12.1, 12.1, 15.1	
	Bezel Width (L/R, U, B) : off bezel based		11.6, 11.1, 16.6	9.8, 9.8, 12.8	
	Vesa		200)	< 200	300 X 300
	WxHxD / weight (w/o stand)		733 x 436 x 72.2 (SPK 76.3) / 5.32kg	974 x 571 x 70.3 (SPK 79.4) / 9.2kg	1,107 x 645 x 70.3 (SPK 79.4) / 12k
	WxHxD / weight (with stand)		733 x 490 x 240.8 / 6.47kg	974 x 619 x 303 / 12.4kg	1,107 x 695 x 303 / 15.0kg
	WxHxD / weight (Carton)		812 x 520 x 190 / 7.95kg	1,147 x 730 x 175 / 15.2kg	1,300 x 775 x 175 / 19.6kg
POWER (Unit : Watts)	Voltage, Hz			100~240V, 50 / 60 Hz	
	Max		68	83	94
	Typical		50	60	70
	Stand-by		0.3↓		
	Energy Saving (Min)		40	50	56
	Energy Saving (Med)		27	35	39
	Energy Saving (Max)		16	19	21
STANDARD APPROVAL	Safety		-	CB, CU TR (for CIS)	
	Environment		CE CE		
	Etc.		ROHS, ErP, Eco Flower (EU only)		
	Eco	ErP Class	A+		++
		On Power	30	37	48
		Consumption (W)			
		Luminance Ratio (%)	65		
		Mercury Content (mg)	0		
		Presence of Lead		Yes	
		Average Annual Consumption (kwh)	44	54	70
		Consumption (kwh)	44	54	70

#### Download LG Commercial Display Mobile App





**You** Tube youtube.com/c/LGECommercialDisplay

All screen images are simulated. Dimension and weights are approximate.

Design, features and specifications subject to change without notice.

Copyright © 2016 LG Electronics Inc. All rights reserved. "LG Life's Good" is a registered trademark of LG Corp.

The names of products and brands mentioned here may be the trademarks of their respective owners.





# LW341H (EU/CIS)

# Comprehensive Hospitality Solution with Pro:Centric®

Now, you can manage your hotel more easily and efficiently with Pro:Centric® series TV models, helping your guests to have a more comfortable and convenient experience in their hotel room. You can also configure and/or update all guest room TVs via a centralized management system, thereby saving cost and workforce.



# LW341H

- Pro:Centric® Application
- Embedded Customizable Templates
- Multiple Channel Spooling
- EZ-Manager
- Swivel Stand

\*Full features are available when the model is connected to the Pro:Centric® server.

#### screen size

32", 43", 49"

### **Key Features**



## Enhanced Guest Experience

• Man

Pro:Centric enables to differentiate guest room experiences with customizable billboards and Electronic Program Guide (EPG) which easily navigates TV channels and program.

### Features

- EPG
- Hotel Information PMS Interfaced Service



# Easy Content Management

Pro:Centric enables centralized and intuitive in-room TV control from the TV settings to content creation and updates.

#### Features

- Embedded Customizable Templates (Added one more template in 2016)
- Up to 8 Hotel Channel Spooling



# Optimized Total Cost of Ownership

Optimize TCO with Pro:Centric® by saving workforce and time for development & management cost for hospitality solutions.

#### Feature

- EZ-Manager 2.1 for more efficient initial configuration
- Remote Management via RF & IP

# **Hospitality Features**



#### **Commercial Swivel Stand**

Expand the rage of comfort for the guests with a commercial grade stand by allowing them to watch a TV from any angle.



#### Welcome Screen/Video

With the capability to display various video formats\* as well as images, Commercial Lite TVs allow for a greater variation of greeting messages in hotel rooms which make customers feel more welcome and cared for.

\* mp4, avi, mov, tp, wma, ts etc.



#### Diagnostics (USB)

Enable service engineers to recognize technical issues of a TV quickly and easily through a USB. The TV stores any technical issues encountered and can output them to a USB device.



#### **External Speaker Out**

Enhance the entertainment experience by adding an additional speaker. Guests listen to and control the TV audio from anywhere in the business areas, including restrooms



# One Channel Map

One Channel Map feature allows users to edit and list the channels of their choice from any of the multiple broadcasting signals.



#### Multi IR

Multi IR function eliminate the remote control signal interference between TVs in multiple dwelling beds.



# Comprehensive Hospitality Solution with Pro:Centric®

# Pro:Centric® V LW341H

Pro:Gentric V

**EU/CIS** 



The Pro:Centric® Application enabled with the Pro:Centric® server provides customizable templates. With those templates, hoteliers can add the hotel branded portal pages and channels. It is also ready for quest-centric services, such as a Welcome Page with the quest's name, Auto Language Setting and Billing Information with the customizable billboard and map pages, etc.

## **Pro:Centric® Features**

## **Enhanced Customer Experience**



Personalize the page with the Pro: Centric® applications(PCA) which improves guests' in-room experience by providing a variety of additional features conveniently just for them.







Wake-up Setting

#### Personalized Pages

When linked with the Property Management System, it provides a Welcome Page with the guest name, Auto Language Setting and Billing information with the guest's name. (From 2016, Arabic, Hebrew, Persian language are also available)

#### Various Additional Features

PCA serves the convenience of the guest through a Wake-up setting, Weather Information, Map Service, and much more functions that you can choose.

# **Easy Content Creation & Management**



You can now differentiate your hotel with our customizable templates and pages which can be specialized for your property. Pro:Centric® provides you a solution that is easily customizable for your



#### • Customizable Template & Page

Choose an alternative look & feel template based on your preference, and edit multiple sections with 40 pages of billboards by yourself with the web based tool. (Max 15pages / section Available)



#### • Multi Channel Spooling


Operation of up to 8 hotel channels (22 sub-channels) can offer various information and added services.

# Dimensions (mm, with stand)

32"


733.2 x 490 x 240.8 6.47kg


\*Swivel



43"


974 x 619 x 303 12.4kg \*Swivel






49"

1,107 x 695 x 303 15.0kg \*Swivel









# Connectivity

- OPTICAL DIGITAL AUDIO OUT
- 2 LAN (MHEG / SERVICE) 2 LNB Satellite IN 3 HDMI IN 1
- 4 H/P OUT
- **6** EXTERNAL SPEAKER OUT
- **6** RGB IN
- **7** RS-232C IN
- ⊕ COMPONENT IN / AV IN
- ANTENNA/CABLE IN 10 HDMI IN 2
- 1 USB IN





HDMI'