

## RC-135Q Wireless Motion Alert

A completely wireless weatherproof sensor which, when triggered, signals an indoor receiver to provide an audio and/or visual alert. Monitors movement in a wide range of home, office, and commercial applications.

### Features:

- Provides audio and/or visual alert when triggered
- Sensor range up to 26ft (8m) at 40° angle at 3ft (1m) height
- Up to 390ft. (120m) transmission range between sensor and receiver<sup>1</sup>
- Plug and play operation, no hardwiring necessary
- Battery operated (3 AAA for sensor and 3 C for receiver). Batteries not included. Receiver can be powered by a 500mA@6VDC power adapter (not included)
- Battery life for sensor is up to 6 months and for receiver is up to 3 months (based on 4 triggers/day on High mode)
- Low battery indicators on sensor and receiver
- 4-position switch: Off, Silent, Low, High
- Mounting hardware included



### Specifications:

Frequency	433.92MHz	
Power	Receiver	1.5VDC C-cell batteries x3 (not included) or 500mA@6VDC power adapter (not included) <sup>2</sup>
	Sensor	1.5VDC AAA batteries x 3 (not included)
Low battery indicators	LEDs flash on sensor and receiver	
Material	ABS plastic, white	
Sound level (receiver)	92dB or 80dB@1ft. (±5dB) or silent (switchable)	
LED indicators (receiver)	3 LEDs flash when sensor activated	
PIR Sensor range	26ft (8m) at 40° angle at 3ft (1m) height	
Transmission range <sup>1</sup>	Up to 390ft (120m)	
IP rating (sensor)	IP44	
Temperature	-4~113°F (-20~45°C)	
Dimensions	Receiver	5 1/8" x 3 13/16" x 1 5/8" (130x96x42mm)
	Sensor	4 3/16" x 3" x 1 7/8" (106x76x48mm)
Weight	Receiver	5-oz (125g)
	Sensor	3-oz (90g)

<sup>1</sup>Transmission range between sensor and receiver will vary depending on installation and environment  
<sup>2</sup>Use 2.1mm

### Additional Products:



Wireless Alert System  
RA-4961-K1Q



Full line of accessories for  
RA-4961-K1Q



Auto Voice Reminder  
AS-1511



Motion Entry Alert  
AS-6111Q

## SECO-LARM® U.S.A., Inc.

16842 Millikan Avenue, Irvine, CA 92606

Phone: (949) 261-2999 | (800) 662-0800 Fax: (949) 261-7326

Website: [www.seco-larm.com](http://www.seco-larm.com) Email: [sales@seco-larm.com](mailto:sales@seco-larm.com)