

Device marker - LS-EMLP (27X18) SR - 0831718

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Device marker, Sheet, silver, unlabeled, can be labeled with: TOPMARK LASER, mounting type: adhesive, lettering field size: 27 x 18 mm



Why buy this product

- Stick-on device marking



Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	
GTIN	4046356926591
Weight per Piece (excluding packing)	19.100 g
Custom tariff number	39191080
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	18 mm
Width (a)	27 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.

General

Color	silver
Components	free from silicone and halogen
Material	TRANSPLY-ABS

Device marker - LS-EMLP (27X18) SR - 0831718

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	54
Adhesive	Acrylic
Printability	Direct laser marking
Device	0831831 TOPMARK LASER
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	800 µm
Adhesive strength	50 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288

UNSPSC

UNSPSC 13.2	39131504
-------------	----------

Device marker - LS-EMLP (27X18) SR - 0831718

Accessories

Accessories

Magazine

Magazine - TOPMARK LASER-MAG SHEET - 0831836

Sheet magazine for TOPMARK LASER



Printing system

Laser marker - TOPMARK LASER - 0831831



Laser marker and MARKING NOTEBOOK with German operating system and German keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit