


REV	1	DATE	ECN NUMBER	2	3	4	5	6	7
005		21 Jun 2017	C03630	ECR COMMENT ADD TEMPERATURE RATING					



General purpose crocodile clip.

Manufactured from bright mild steel.
Large (30mm) jaw opening makes it suitable as a battery clip.
The integral cable clamp has a secure 4mm screw fixing.
The enhanced finger grip ensures a simple operation.

CLIP	
MATERIAL	: Bright Mild Steel CS4, nickel plated : Temperature Rating -20 to + 200°C
SCREW / NUT & WASHER	: M4 x 6mm, Steel, Nickel plated
Current Rating	: 25 Amps
RATED VOLTAGE:	: 50V



PVC INSULATED BOOT AVAILABLE IN
RED 310-0500 OR BLACK 310-0100
OPERATING TEMPERATURE WITH BOOT FITTED -20 TO +60°C

DELTRON Components			PROPRIETARY AND CONFIDENTIAL:		IF IN DOUBT ASK! DO NOT SCALE DRAWING!		AUTHOR Shaun Barron		TITLE LARGE CROCODILE				
DELTRON Enclosures			THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ALPHA 3 MANUFACTURING . ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ALPHA 3 MANUFACTURING IS PROHIBITED.		UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETRES. LINEAR & RADIAL TOLERANCE:		EDITOR DT		FILE 304-0000				
ROXBURGH EMC			DEM Manufacturing is a division of Alpha 3 Manufacturing LTD. DEM Manufacturing, Deltron Emcon House, Hargreaves Way, Sawcliffe Ind. Park, Scunthorpe, North Lincolnshire, DN15 8RF, UK.		NO DECIMAL PLACES 1 DECIMAL PLACE 2 DECIMAL PLACES ANGULAR TOLERANCE:		APPROVER DT		PART 304-0000				
+44(0)1724 273200		www.dem-uk.com		THE FINISHED PRODUCT SHOULD BE CLEAN AND FREE FROM ALL LIQUIDS AND DEBRIS. SURFACES SHOULD BE OF UNIFORM APPEARANCE. FREE FROM SHARP EDGES, BURRS AND CORROSION		THIRD ANGLE PROJECTION		SHEET 1 OF 1		ISSUE/REV. 005		VERSION 7	
								SCALE 1:1 A4		RELEASED		EDIT DATE 21 Jun 2017	