



Philips Softone
Energy saving bulb

12 W (51 W)

Bayonet cap
Warm white

871150066261390

Soft and gentle energy saving light

Creates an ambience to suit your mood

No more harsh, unattractive light. Softone energy savers give a soft light that is gentle to your eyes. There is a choice of light effects. From invigorating cool light for working to warm light for relaxing.

Soft light effect

- Gives a soft, diffused light that is gentle on your eyes

Perfect shape

- Looks like a standard lamp

Sustainable choice

- Saves up to 78% energy and lasts 10 years

PHILIPS

Energy saving bulb
12 W (51 W) Bayonet cap, Warm white

Specifications

Technical specifications

- Power factor: 0.6
- Starting time: 1 s
- Mercury content: 1.4 mg
- Lifetime of lamp: 10 year(s)
- Rated lifetime: 10 year(s)
- Rated power: 12 W
- Wattage: 12 W
- Wattage equivalent: 51 W
- Lamp dimension (width): 60.8 mm
- Colour rendering index (CRI): 82
- Lamp current: 90 mA
- Lamp dimension (height): 112.5 mm
- Lumen: 610
- Rated luminous flux: 610 lm
- Colour temperature: 2700 K
- Lifetime of lamp: 10,000 hour(s)
- Rated lifetime: 10,000 hour(s)

- Number of switch cycles: 20,000
- Lumen maintenance factor: 0.65 (at the end of the nominal lifetime) %
- Warm up time 60% light output: 10–80 s
- Voltage: 230–240 V
- Energy efficiency label: A
- Fitting/Cap: B22
- Shape: Bulb
- Dimmable: No
- Colour: Warm White
- Light effect/finish: White
- Wattage standard bulb: 51 W

Cleaning up breakages and disposal

- Cleaning: Follow the advice for proper clean up*
- Disposal: Follow the instruction for disposal as special waste**

871150066261390

Highlights

Soft light gentle to your eyes

Fully and evenly illuminated, these Philips lamps give a diffused light effect without any dazzle or glare.

Looks like a standard lamp

Identical shape and size, looks just like your standard bulb and has the perfect fit.

Saves up to 78% energy and lasts 10 years

Save up to 78% energy compared to your standard bulb with this Philips energy saving light bulb. It pays for itself and lasts 10 times as long. So reduce your energy bill and start saving now, year after year.



Issue date 2014-09-22

Version: 1.0.1

12 NC: 9297 522 31418
EAN: 87 11500 66261 3

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

** Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.