





6-Lobe Pin



6-Lobe Pin - Raised Countersunk Machine Screw - A2 Stainless Steel



Dimensions (mm)

	SCREW TYPE	M3.5
	6-LOBE PIN	
	DIMENSIONS	
COUNTERSUNK HEAD		6.4
		1.8

Material and Finish

Material: A2 Stainless Steel
Heat Treatment: None
Finish: Passivated

Part Numbers & Driver Size


GAUGE \ LENGTH	12mm	20mm	25mm	30mm	35mm	40mm	50mm	75mm	DRIVER SIZE
	M3.5	RTRM3512	RTRM3520	RTRM3525	RTRM3530	RTRM3535	RTRM3540	RTRM3550	

Additional Information

Installation: 6-Lobe Pin - see video
Removal: 2-Way Removable Screw

Hafren
6-Lobe Pin

- ✓ 6-Lobe drive with internal pin
- ✓ High torque drive
- ✓ Available in multiple heads & threads
- ✓ Stocked in the largest range available



Every effort has been made to ensure the accuracy of information provided in this datasheet. Hafren Fasteners cannot warrant the information however, expressly or implied, and any liability arising from it is expressly excluded. Customers must satisfy themselves as to the suitability of products and the technical information relating to them, and it is recommended that you conduct your own tests to establish suitability. All sizes shown are in mm without min and max tolerances and are guide sizes. Hafren Fasteners reserve the right to change/alter sizes without notice. This does not effect your statutory rights.

6-Lobe Pin



Weight per Pack


LENGTH \ GAUGE	12mm	20mm	25mm	30mm	35mm	40mm	50mm	75mm	DRIVER SIZE
M3.5	Box 9 108g	Box 9 156g	Box 9 182g	Box 12 208g	Box 12 240g	Box 18 269g	Box 18 333g	Box 22 485g	T10

*All parts packed in 100pcs - Please see below pack Dimension guide

Pack Dimensions Guide

BOX SIZE \ DIMENSION	BOX 9	BOX 12	BOX 18	BOX 22	BOX 27	BOX 30	BOX 32
A	51mm	57mm	71mm	81mm	89mm	101mm	114mm
B	32mm	36mm	47mm	54mm	68mm	76mm	82mm
C	55mm	66mm	90mm	111mm	124mm	128mm	171mm

Cardboard Box



Every effort has been made to ensure the accuracy of information provided in this datasheet. Hafren Fasteners cannot warrant the information however, expressly or implied, and any liability arising from it is expressly excluded. Customers must satisfy themselves as to the suitability of products and the technical information relating to them, and it is recommended that you conduct your own tests to establish suitability. All sizes shown are in mm without min and max tolerances and are guide sizes. Hafren Fasteners reserve the right to change/alter sizes without notice. This does not effect your statutory rights.