

Pozidriv® Bits

The ideal multi-purpose tools to meet production requirements for both quality and performance

Impact resistant
modified CVM, tool
steel, hardened



Suitable for all
applications for both
manual and machine
Hardness HRC 59-61

PoziDriv® Insert & Power Bits



712 Pozidriv® Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71200	0	25	10	.10
71201	1	25	10	.10
71202	2	25	10	.10
71203	3	25	10	.10



2 bit
pack

712 Pozidriv® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
71250	0	25	.03
71251	1	25	.03
71252	2	25	.03
71253	3	25	.04



71254 Pozidriv® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

71254 Set includes the following bits:

wt. .04 1, 2, 3 x 1" (25mm)



2 bit
pack

777 Pozidriv® Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77710	#1 + #2	30



742 Pozidriv® Power Bits, 1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74203	1	50	10	.24
74212	2	50	10	.25
74221	3	50	10	.26



2 bit
pack

742 Pozidriv® Power Bit Packs, 2"

CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
74261	1	50	.06
74262	2	50	.06
74263	3	50	.07



742 Pozidriv® Power Bits, 1/4" Hex Drive, Length 2.75"/70mm

Item			
No.	Size	mm	pkg.
74201	0	70	10
74205	1	70	10
74214	2	70	10



2 bit
pack

739 Pozidriv® Power Bits, 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack

Item			
No.	Size	mm	pkg.
73901	0	70	1
73902	1	70	1
73903	2	70	1



742 Pozidriv® Power Bits, 1/4" Hex Drive, Length 3.5"/90mm Single Pack

Item				
No.	Size	mm	pkg.	lbs.
74231	1	90	1	.03
74232	2	90	1	.04
74233	3	90	1	.05



10 bit pack

742 Pozidriv® Power Bits, 1/4" Hex Drive, Length 3.5"/90mm 10 Bit Pack

Item				
No.	Size	mm	pkg.	lbs.
74236	1	90	10	.34
74237	2	90	10	.46
74238	3	90	10	.53

Wiha Stainless Steel Pozidriv® Insert & Power Bits



712 Stainless Steel Pozidriv® Insert Bits, 1/4"

Item			
No.	Size	mm	pkg.
71241	1	25	1
71243	3	25	1



704 Stainless Steel Pozidriv® Power Bits, 1/4" Hex Drive, Length 2.0"/50mm

Item			
No.	Size	mm	pkg.
70407	1	50	1
70410	3	50	1

Wiha Pozidriv® Power Blades



760 Pozidriv® Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Size	lbs.	pkg.
76011	1	.03	1
76012	2	.04	1
76013	3	.04	1



76091 3 Piece Pozidriv® Blade Set

Item		
No.	lbs.	Pozidriv®: #1, 2,
76091	.12	3 x 90mm