


Wiha Phillips Power Bit Packs



714 Phillips Double End Bits
1/4" Hex Drive, Length 2.36"/60mm

Item	+	+	+	+	+
No.	Size	Size	mm	pkg.	lbs.
71404	1 x 1	60	10	.31	
71414	2 x 2	60	10	.31	
71424	3 x 3	60	10	.32	



2 bit pack



714 Phillips Double End Power Bit Packs, 60mm OAL

Item	+	+	+	+
No.	Size	Size	mm	lbs.
71464	1 + 1	60	.07	
71465	2 + 2	60	.07	
71466	3 + 3	60	.07	



743 Slotted & Phillips Double End Bits, 1/4" Hex Drive, Length 2.36"/60mm

Item	+	+	+	+	+
No.	mm	Size	mm	pkg.	lbs.
74303	4.5 x 1	60	10	.22	
74306	5.5 x 2	60	10	.30	
74309	7.0 x 3	60	10	.32	



2 bit pack



743 Slotted/Phillips Double End Power Bit Packs, 60mm OAL

Item	+	+	+	+
No.	mm	Size	mm	lbs.
74304	4.5 + 1	60	.07	
74308	5.5 + 2	60	.07	
74310	7.0 + 3	60	.07	

Wiha Stainless Steel Phillips Insert Bits & Power Bits



711 Stainless Steel Phillips Insert Bits, 1/4"

Item	+	+	+
No.	Size	mm	pkg.
71133	1	25	1
71134	2	25	1
71135	3	25	1



704 Stainless Steel Phillips Power Bits, 1/4"

Item	+	+	+
No.	Size	mm	pkg.
70401	1	50	1
70402	2	50	1
70405	3	50	1


Terminal Block Xeno Bits



714 Xeno Combination Terminal Block Power Bits, 1/4" Hex Drive, OAL 2.0"/50mm

Item	+	+	+	+
No.	Size	mm	pkg.	lbs.
71452	1	50	10	.24
71453	2	50	10	.25

2 bit pack



714 Xeno Combination Terminal Block Power Bit Packs, 2" CVM S2 modified tool steel

Item	+	+	+
No.	Size	mm	lbs.
71455	1	50	.06
71456	2	50	.06

Wiha Phillips Power Blades & Power Blade Holder



760 Phillips Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item	+	+	+
No.	Size	lbs.	pkg.
76041	0	.01	1
76042	1	.02	1
76043	2	.03	1
76044	3	.04	1



76094 4 Piece Phillips Blade Set

Item	+	+	+
No.	lbs.	Phillips:	Set includes:
76094	.17	#0, 1, 2,	3 x 90mm



76000 CentroFix Cushion Grip Blade Holder

Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26