

› Logic Controller em4 & Millenium Evo interface

Bluetooth interface

- › Connect via Smartphone or PC
- › Access to your PLC with Crouzet Virtual Display or directly in Crouzet Soft
- › Program, parameters modification, and download datalogs nearby your installation





Bluetooth interface

Specific characteristics	
Part number	88 980 112
Finish	Glossy black
Color	Black RAL 9011
Plastic parts Certification	UL94 V0, 1272/2008/CE (Halogen free)
General characteristics	
Products certification	CE, cURus Listed
Conformity with the RED directive (in accordance with 2014/53/EU)	EN 300 328 V2.1.1 : Radio essential requirements EN 301 489-17 V3.1.1 : EMC essential requirements EN 301 489-1 V2.1.1 : EMC essential requirements EN 62479 :2010: Health essential requirements EN 60950-1 :2006 + A11:2009 + A1:2010 + A12:2012 + A2:2013 : Safety essential requirements
Frequency range, power	2402 - 2480 MHz, +3dBm
Operation temperature	20 (-4 °F) → +60°C (140 °F) (+40°C (104 °F) in a non-ventilated enclosure) UL : Maximum surrounding air temperature of 50°C
Storage temperature	40 (-40 °F) → +80°C (176 °F)
Relative humidity	95% max. (no condensation or dripping water)
Maximum utilization altitude	Operation: 2000 m Transport: 3000 m
Resistance to electrostatic discharge	Immunity to ESD IEC/EN 61000-4-2, level 3
Resistance to HF interference (Immunity)	Immunity to radiated electrostatic fields IEC/EN 61000-4-3, level 3 Immunity to fast transients (burst immunity) IEC/EN 61000-4-4, level 3 Immunity to shock waves IEC/EN 61000-4-5 Radio frequency in common mode IEC/EN 61000-4-6, level 3
Conducted and radiated emissions (in accordance with EN 55032)	Class B
Protocol	Bluetooth ≥ V4.2
Hardware compatibility	Base 24 VDC power supply version
Max. absorbed power	0.25W @ 3.3V
Software compatibility	Windows W7 min, Android 4.3 min
Protection rating (in accordance with IEC/EN 60529)	IP 20
Range	≤ 10 m
Weight	Without packing: 9 g With packing: 15 g
Dimensions	Without packing: 35 x 36 x 12 mm / 1.38 x 1.42 x 0.47 inch With packing: 80 x 140 x 30 mm / 3.15 x 5.51 x 1.18 inch

Technical sketches

Dimensions (mm)

Bluetooth interface



PRELIMINARY

Warning:

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet Automatismes SAS and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.