

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0934452501

Status:

Active

Overview:

ML-XT Sealed Connection System

Description:

ML-XT Sealed 3 Circuit Plug Housing with Heatshrink, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

Drawing (PDF)

Product Specification 934430010-P (PDF)

Application Specification 934430010-A (PDF)

Packaging Specification 934430002-K (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Part Link

Overview

Product Literature Order No

Product Name

UPC

Crimp Housings

93445

Power, Signal, Wire-to-Wire

63824-5300

ML-XT Sealed Connection System

987651-0201

ML-XT

889056191487

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Temperature Range - Operating

3

Black

Plug

No

None

Yes

Nylon

7.644/g

2

Bag

No

N/A

Yes

-55°C to +125°C

Electrical

Current - Maximum per Contact

13.0A

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

934430010-A

934430002-K

934430010-P

934430020-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Reviewed

Not Reviewed

Search Parts in this Series

93445 Series

Mates With

ML-XT Sealed 3 Circuit Receptacle Housing 93444-2501

Use With

ML-XT Female (Socket) Terminal 84525-0009 (Nickel), ML-XT Female (Socket) Terminal 84525-0032 (Selective Gold), ML-XT 3 Circuit Plug Wedgelock 93448 , ML-XT Blind Cavity Plug 93494-1000

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for ML-XT Sealed Connection System and Crimp Terminals	<u>0638245300</u>

This document was generated on 05/02/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION