



CorePro LEDbulbs

CorePro LED bulb 12.5-100W A60 E27 840

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost. The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Wattage Equivalent	
Cap-Base	E27 [E27]	100 W	
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	
Switching Cycle	50000X	0.5 s	
Technical Type	12.5-100W	Warm Up Time to 60% Light (Nom)	
Light Technical		0.5 s	
Color Code	840 [CCT of 4000K]	Power Factor (Nom)	
Beam Angle (Nom)	200 °	0.5	
Luminous Flux (Nom)	1521 lm	Voltage (Nom)	
Luminous Flux (Rated) (Nom)	1521 lm	220-240 V	
Color Designation	Cool White (CW)	Temperature	
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	
Luminous Efficacy (Rated) (Nom)	121.68 lm/W	90 °C	
Color Consistency	<6	Controls and Dimming	
Color Rendering Index (Nom)	80	Dimmable	
LLMF At End Of Nominal Lifetime (Nom)	70 %	No	
Operating and Electrical		Mechanical and Housing	
Input Frequency	50 to 60 Hz	Bulb Finish	
Power (Rated) (Nom)	12.5 W	Frosted	
Lamp Current (Nom)	115 mA	Approval and Application	
Product Data		Energy Efficiency Label (EEL)	
Full product code		A+	
Order product name		Energy Consumption kWh/1000 h	
		13 kWh	
		Product Data	
		Full product code	
		871869651030800	
		Order product name	
		CorePro LED bulb 12.5-100W A60 E27 840	

CorePro LEDbulbs

EAN/UPC - Product	8718696510308
Order code	929001312402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001312402
Net Weight (Piece)	0.076 kg



Dimensional drawing




A60 220-240V 12.5W-100W 4000K E27 ND

Product	D	C
CorePro LED bulb 12.5-100W A60 E27 840	60 mm	110 mm

Photometric data




CorePro LEDbulb 100W E27 840 FR A60




CorePro LEDbulb 100W E27 840 FR A60

Lifetime



LEDbulb 100W E27 840 FR A60



LEDbulb 100W E27 840 FR A60

