


Flex Strap

Cable Wraptor® Flexible Straps offer a reusable, versatile, lightweight organizational solution without a wasted "tail". Just wrap, tighten, then cut and wrap again! Stretchable, flexible material won't damage delicate cables and cords.

- Re-usable. Thread the tail backward through the last slot used, and pull to release the strap.

- 12" long strap with finger grips on the end and tail.
- Malleable material will stretch up to 300%.
- Thread 2 slots for a stronger hold on bundle.
- Interlinkable - thread multiple straps together for greater lengths.



Length	Part #	Pkg Qty	Tensile Strength	Description	Bundle Dia. Min.	Bundle Dia. Max.	Color
12"	45-812UVB	10/bag	20 lb	Flexstrap	0.25"	3¼"	Black
	45-824UVB	24/bag	20 lb	Flexstrap	0.25"	3¼"	Black
	45-812GN	12/bag	20 lb	Flexstrap	0.25"	3¼"	Green
	45-824GN	24/bag	20 lb	Flexstrap	0.25"	3¼"	Green
	45-812N	12/bag	20 lb	Flexstrap	0.25"	3¼"	Natural
	45-824N	24/bag	20 lb	Flexstrap	0.25"	3¼"	Natural



Xtreme Ties

Xtreme Ties save the day in harsh environment applications. Specifically designed to perform under intense UV and cold weather conditions.

Engineered from improved Nylon 66 - ISO certified to maintain its properties to -40°F/C.

- Enhanced UV protection.
- UL Listed for indoor and outdoor applications from -4°F - 185°F (-20°C - 85°C). UL Type 21.

Length	Part #	Pkg Qty	Tensile Strength	Description	Bundle Dia. Max.	Color
8"	45-308UVBFZ	20	50 lb	Flexstrap	2"	Black
11"	45-311UVBFZ	20	50 lb	Flexstrap	3"	Black
14"	45-314UVBFZ	20	50 lb	Flexstrap	4"	Black
8"	46-308UVBFZ	100	50 lb	Flexstrap	2"	Black
11"	46-311UVBFZ	100	50 lb	Flexstrap	3"	Black
14"	46-314UVBFZ	100	50 lb	Flexstrap	4"	Black



NEW Self Cutting

Save time and frustration using the latest innovation from Gardner Bender, a self-cutting cable tie. Simply lock and twist to finish the job, with no need for additional tools!

- Min/Max operating temperature -40° to 185°F (-40° to 85°C).
- Multi-purpose use.

- No tools required! Simply twist and tear.
- Durable stainless steel blade for a clean cut everytime.
- Patented design.



Length A	Part #	Pkg. Qty	Tensile Strength	Description	Color
8"	45-308SC	20/bag	50 lb	Cable Tie, Self Cutting	Natural
	45-308UVBSC	20/bag	50 lb	Cable Tie, Self Cutting	Black
	46-308SC	50/bag	50 lb	Cable Tie, Self Cutting	Natural
	46-308UVBSC	50/bag	50 lb	Cable Tie, Self Cutting	Black
11"	45-311SC	20/bag	50 lb	Cable Tie, Self Cutting	Natural
	45-311UVBSC	20/bag	50 lb	Cable Tie, Self Cutting	Black
	46-311SC	50/bag	50 lb	Cable Tie, Self Cutting	Natural
	46-311UVBSC	50/bag	50 lb	Cable Tie, Self Cutting	Black
14"	45-314SC	20/bag	50 lb	Cable Tie, Self Cutting	Natural
	45-314UVBSC	20/bag	50 lb	Cable Tie, Self Cutting	Black
	46-314SC	50/bag	50 lb	Cable Tie, Self Cutting	Natural
	46-314UVBSC	50/bag	50 lb	Cable Tie, Self Cutting	Black

