

Wiha Security TORX® Insert Bits and Power Bits

Tamper Resistant Torx®

Made by Wiha -
Production
Quality



Security TORX®



Impact resistant modified
CVM tool steel, hardened

Highly resistant
to wear and
tear for a
long tool life


Suitable for all applications
for both manual and machine
Hardness HRC 59-61



701 Security TORX® Bits, 1/4"

Item					
No.	Size	mm	pkg.	lbs.	
70127	T7s	25	10	.12	
70128	T8s	25	10	.12	
70129	T9s	25	10	.12	
70135	T10s	25	10	.12	
70139	T15s	25	10	.12	
70142	T20s	25	10	.12	
70148	T25s	25	10	.12	
70160	T27s	25	10	.13	
70163	T30s	25	10	.13	
70168	T40s	25	10	.14	

2 bit
pack



701 Security TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item					
No.	Size	mm	lbs.		
70150	T7s	25	.03		
70151	T8s	25	.03		
70152	T9s	25	.03		
70153	T10s	25	.03		
70154	T15s	25	.03		
70155	T20s	25	.03		
70156	T25s	25	.03		
70157	T27s	25	.03		
70158	T30s	25	.03		
70159	T40s	25	.03		



5/16"

725 Security TORX® Bits, 5/16"

Item					
No.	Size	mm	pkg.	lbs.	
72542	T40s	35	10	.28	
72547	T45s	35	10	.32	
72552	T50s	35	10	.34	
72557	T55s	35	10	.52	

2 bit
pack



725 Security TORX® Bits, 5/16" 2 Bit Pk.

Item					
No.	Size	mm	lbs.		
72562	T40s	35	.28		
72563	T45s	35	.29		
72564	T50s	35	.30		
72567	T55s	35	.32		

5 bit packs



Made in Taiwan

745 Protturn Security TORX® Power Bits 1/4" Hex Drive, Length 3.0"/75mm

Item					
No.	Size	mm	pkg.	lbs.	
74566	T10s	75	5	.01	
74568	T15s	75	5	.01	
74570	T20s	75	5	.01	
74572	T25s	75	5	.02	
74574	T27s	75	5	.02	
74576	T30s	75	5	.03	



705 Security TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item					
No.	Size	mm	pkg.	lbs.	
70507	T7s	50	10	.18	
70508	T8s	50	10	.18	
70509	T9s	50	10	.18	
70510	T10s	50	10	.19	
70515	T15s	50	10	.19	
70520	T20s	50	10	.21	
70525	T25s	50	10	.23	
70527	T27s	50	10	.23	
70530	T30s	50	10	.23	
70540	T40s	50	10	.23	
70545	T45s	50	10	.33	
70550	T50s	50	10	.37	
70555	T55s	50	10	.37	


2 bit
pack



705 Security TORX® Power Bit Packs, 2"

Item					
No.	Size	mm	lbs.		
70556	T7s	50	.07		
70557	T8s	50	.07		
70558	T9s	50	.07		
70559	T10s	50	.07		
70560	T15s	50	.07		
70561	T20s	50	.07		
70562	T25s	50	.07		
70563	T27s	50	.07		
70564	T30s	50	.07		
70565	T40s	50	.07		
70566	T45s	50	.08		
70567	T50s	50	.08		
70568	T55s	50	.09		

5 bit packs



705 Security TORX® Power Bits 1/4" Hex Drive, Length 3.5"/90mm

Item					
No.	Size	mm	pkg.	lbs.	
70533	T10s	90	5	.02	
70534	T15s	90	5	.02	
70535	T20s	90	5	.02	
70536	T25s	90	5	.02	
70537	T27s	90	5	.03	
70538	T30s	90	5	.03	