

3 in 2 FlexCage MB973SP-1B

HDD BAY

ICY DOCK®
www.icydock.com

Tray-less 3.5" SATA Removable RAID Backplane Module



2x
5.25" BAYS

2x 4 Pin MOLEX or 2x 15 Pin SATA POWER
POWER UP 3 DRIVES

3x 3.5" SATA
HARD DRIVES



Included 4 pin to 15 pin
adapter cables

Multi-Locking latch mechanism
Prevent a door from being opened easily



Active Power LED

Only active when HDD is inserted



3
YEARS
WARRANTY



Efficient Cooling



3 Pin & 2 Pin Fan Connector
COMPATIBLE WITH MOST
80MM COOLING FAN



Active Power Technology power system

HDD IN



HDD OUT



MB973SP-1B Key Features

- Fits 3 x 3.5" SATA HDD into 2 x 5.25" Device Bays.
- Supports SATA 3 (6 Gb/s) hard drives.
- Compact and space saving design to fit multiple drives.
- Commercially designed for servers & rackmounts.
- Screw-less, tool-less design for genuine plug & play and hot swap use.
- Lightweight aluminum body construction for durability & heat dissipation.
- 80mm cooling fan for maximum air flow.
- Fan is replaceable with aftermarket fans that use standard 2-pin or 3-pin connectors.
- Flex Fit Design – accommodates different 5.25" tab lengths for server or tower cases.
- Active Power Technology (APT) - individual blue led & cooling fan only powers up if there is a drive installed in the bay.
- Multi-locking door latches to prevent accidental drive ejection.
- Two 4 pin to 15 pin adapter cable included for 15 pin SATA power ports.
- ICY DOCK 3 year warranty equivalent to hard drive manufacturer warranty to ensure maximum reliability and long life.

SATA 6Gbps

Model Number	MB973SP-1B
Color	Black
Drive Fit	3 x 3.5" SATA 1.5 / 3 / 6 Gbit/s hard drives
Drive Bay	2 x 5.25" half height device bay
Host Interface	3 x 7 pin SATA port
Power Input	4 pin power port x 2 or 15 pin power port x 2 (4 to 15 pin adapter cables Included)
Transfer Rate	Up to 6Gb/sec. (depending on hard drive speed)
Insert& Extract connection via	Direct SATA hard drive connection
Structure	Aluminum body w/ partial plastic
Drive Cooling	Replaceable 80 x 80 x 25mm cooling fan Compatible with most 80mm fans with 2pin/ 3pin connector Metal chassis heat dispersion
Power Indicator	Blue LED
HDD Access Indicator	Flashing blue LED
Dimension (L x W x H)	146.4 x 85.8 x 200.4mm
Weight	1.97 lbs