


Wiha Protturn Precision Screwdrivers



95190 6 Pc. Slotted/Phillips Protturn Precision Screwdriver Set Molded on precision handle. Blade high alloy CVM tool steel, black finish.

Item	Slotted: 1.5x40mm	lbs.
No.	2.5x50mm, 3.5x60mm	

95190	Phillips: 00x40mm, 0x50mm, 1x60mm	.27
-------	-----------------------------------	-----



65090 9 Pc. Slotted/Phillips Protturn Precision Screwdriver Set Molded on precision handle. CVM tool steel, black finish blades.

Item	Slotted:
No.	1.5x40mm, 2.0x5.0mm,
65090	2.5, 3.0, 3.5, 4.0x60mm
	Phillips: 00x40mm, 0x50mm, 1x60mm



96800 Protturn Precision Chip Lifter Molded on precision handle. Blade CVM tool steel, hardened, black finish.

Item	Size	mm	mm	Inch	lbs.	pkg.
No.						
96800	1.0	50	145	5.7	.07	1



62990 5 Piece Slotted & Phillips Pocket Pack Set Wiha Protturn precision ball retainer handle & 4 Wiha interchangeable blades.

62990 Set includes the following blades:

- ↓ Slotted: 1.5, 2.0, 3.0, 4.0mm
- ⊕ Phillips: #000, #00, #0, #1

lbs. .15



62993 9 Pc. Slotted/Phillips/TORX® Work Station Set Wiha Protturn precision ball retainer handle & 8 Wiha interchangeable blades.

62993 Set includes the following blades:

- ↓ Slotted: 1.5, 2.0, 3.0, 4.0mm
- ⊕ Phillips: #000, #00, #0, #1
- ⊗ TORX®: T6, T7, T8, T9, T10, T15, T20

lbs. .64



62995 22 Pc. Slotted/Phillips/TORX®/Ball End Hex Inch & Metric Tech Pack Wiha Protturn precision ball retainer handle & 21 interchangeable blades. In canvas storage pouch

62995 Set includes the following blades:

- ↓ Slotted: 1.5, 2.0, 3.0, 4.0mm
- ⊕ Phillips: #000, #00, #0, #1
- ⊗ TORX®: T6, T7, T8, T9, T10, T15, T20
- ⬢ Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⬢ Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .87

62994 14 Pc. Inch/Metric Ball End Hex Work Tech Pack Protturn precision ball retainer handle & 13 Wiha interchangeable blades.

62994 Set includes the following blades:

- ⬢ Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⬢ Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .66

Set in canvas storage pouch

Wiha Magnetizer/Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

Shatterproof Box is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

40010 Magnetizer and Demagnetizer

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.

Application:

To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

Item	Dimensions	lbs.
No.		
40010	2.1" x 2.0" x 1.1"	.30

(Parts under 1" Length or 1/8" Diameter may not demagnetize)