

TDK Corporation
 MAGNETICS BG
 GM
 Teppei Watanabe

CLF (Consumer applications) series Product Discontinuation Notice

First of all, we would like to thank you very much for your continuous cooperation with TDK and our products. This letter informs your company that TDK is planning to discontinue and stop production of the certain products we have been currently shipping to you. Due to product profitability or products elimination and unification, we had to decide to discontinue manufacturing the products listed below. This list not only shows cross-reference between your part number and our part number for each of end-of-life products, but also exhibits TDK part numbers of recommended alternative products wherever available. We deeply regret to inform you of this discontinuation. However, because of above reason, please let us ask you for considering replacement with TDK's alternative product wherever possible. If there is no TDK's alternative product available, then we have to ask you to kindly look into other sources in the market.

Description

| Your product name | Our product name | Our substitute |
|-------------------|------------------|----------------|
| 2345099 | CLF10040T-100M | VLS6045EX-100M |
| 2345100 | CLF10040T-101M | VLS6045EX-101M |
| 2345101 | CLF10040T-150M | VLS6045EX-150M |
| 2345102 | CLF10040T-151M | VLS6045EX-151M |
| 2345103 | CLF10040T-1R0N | VLS6045EX-1R0N |
| 2345104 | CLF10040T-1R5N | VLS6045EX-1R5N |
| 2345105 | CLF10040T-220M | VLS6045EX-220M |
| 2345106 | CLF10040T-221M | VLS6045EX-221M |
| 2345107 | CLF10040T-2R2N | VLS6045EX-2R2N |
| 2345108 | CLF10040T-330M | VLS6045EX-330M |
| 2345111 | CLF10040T-331M | |
| 2345112 | CLF10040T-3R3N | VLS6045EX-3R3N |

Affected products : Please refer to product name listed below.

1. Please send us the final required quantity information for listed EOL product.
 Received date of Last Time Buy order : **March 29, 2019**
2. The final delivery date : **September 30, 2019**

After receiving this letter, please send the acknowledgement to TDK local salesperson who is currently serving you. We apologize for any inconveniences raised by this discontinuation of products, but do hope we will have your kind understanding and your cooperation soon.

Sincerely yours,

| | |
|--------|---|
| Accept | <p style="margin-left: 40px;">Company _____</p> <p style="margin-left: 40px;">Department _____</p> <p style="margin-left: 40px;">Name _____</p> |
|--------|---|

| Your product name | Our product name | Our substitute |
|-------------------|------------------|----------------|
| 2345113 | CLF10040T-470M | VLS6045EX-470M |
| 2345114 | CLF10040T-4R7N | VLS6045EX-4R7M |
| 2345115 | CLF10040T-680M | VLS6045EX-680M |
| 2345116 | CLF10040T-6R8N | VLS6045EX-6R8M |
| 2360977 | CLF12555T-100M | VLS6045EX-100M |
| 2360978 | CLF12555T-101M | VLS6045EX-101M |
| 2360979 | CLF12555T-150M | VLS6045EX-150M |
| 2360980 | CLF12555T-151M | VLS6045EX-151M |
| 2360981 | CLF12555T-1R0N | VLS6045EX-1R0N |
| 2360982 | CLF12555T-1R5N | VLS6045EX-1R5N |
| 2360983 | CLF12555T-220M | VLS6045EX-220M |
| 2360984 | CLF12555T-221M | VLS6045EX-221M |
| 2360985 | CLF12555T-2R2N | VLS6045EX-2R2N |
| 2360987 | CLF12555T-330M | VLS6045EX-330M |
| 2360988 | CLF12555T-331M | |
| 2360989 | CLF12555T-3R3N | VLS6045EX-3R3N |
| 2360990 | CLF12555T-470M | VLS6045EX-470M |
| 2360991 | CLF12555T-471M | |
| 2360992 | CLF12555T-4R7N | VLS6045EX-4R7M |
| 2360993 | CLF12555T-680M | VLS6045EX-680M |
| 2360994 | CLF12555T-6R8N | VLS6045EX-6R8M |
| 2360920 | CLF6045T-100M | VLS6045EX-100M |
| 2360921 | CLF6045T-101M | VLS6045EX-101M |
| 2360922 | CLF6045T-150M | VLS6045EX-150M |
| 2360923 | CLF6045T-151M | VLS6045EX-151M |
| 2360924 | CLF6045T-1R0N | VLS6045EX-1R0N |
| 2360926 | CLF6045T-1R5N | VLS6045EX-1R5N |
| 2360927 | CLF6045T-220M | VLS6045EX-220M |
| 2360928 | CLF6045T-221M | VLS6045EX-221M |
| 2360929 | CLF6045T-2R2N | VLS6045EX-2R2N |
| 2360930 | CLF6045T-330M | VLS6045EX-330M |
| 2360931 | CLF6045T-331M | |
| 2360932 | CLF6045T-3R3N | VLS6045EX-3R3N |
| 2360933 | CLF6045T-470M | VLS6045EX-470M |
| 2360934 | CLF6045T-471M | |
| 2360935 | CLF6045T-4R7N | VLS6045EX-4R7M |
| 2360936 | CLF6045T-680M | VLS6045EX-680M |
| 2360938 | CLF6045T-6R8N | VLS6045EX-6R8M |
| 2345081 | CLF7045T-100M | VLS6045EX-100M |
| 2345094 | CLF7045T-101M | VLS6045EX-101M |
| 2345082 | CLF7045T-150M | VLS6045EX-150M |
| 2345095 | CLF7045T-151M | VLS6045EX-151M |
| 2345083 | CLF7045T-1R0N | VLS6045EX-1R0N |
| 2345084 | CLF7045T-1R5N | VLS6045EX-1R5N |
| 2345085 | CLF7045T-220M | VLS6045EX-220M |
| 2345096 | CLF7045T-221M | VLS6045EX-221M |
| 2345086 | CLF7045T-2R2N | VLS6045EX-2R2N |
| 2345090 | CLF7045T-330M | VLS6045EX-330M |

| | |
|--------|--|
| Accept | |
| | <p>Company _____</p> <p>Department _____</p> <p>Name _____</p> |