Diamond Drill Bits

Page 1 of 2

Diamond Drill Bit Set 6 – 12mm



Drills produce perfect holes in Porcelain, Stone, Granite and Marble

Set suitable for producing holes required to take plugs for attaching most bathroom accessories

High quality sintered diamond tips Metal and diamond powder mixed, pressed then sintered to create multiple layers of diamond Sintered tips are brazed onto a 40 CR steel body with silver by inductive brazing

Tip can be revived when initially worn, by exposing new diamond layers by drilling into an aluminium oxide grinding stone, concrete or any abrasive stone to revive the cutting surface


Working drill life at least 3 x longer than electroplated diamond drill bits

Also available in individual sizes 6 -14mm with Hex. shank and 22 - 45mm with M14 internal threads

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
DIA-00200	Diamond Drill Bit Set 6, 8, 10 & 12mm	271	210	40	220

Diamond Drill Bits with Hex Shank



Small range individual Diamond Drill Bits 6 – 14mm Wet cutting

Quick change 1/4" Hex-Shanks

Supplied with Drill Guide/Dust Catcher with 6 self adhesive non slip pads

Cutting speed:

For best results use 2500 – 3000 RPM

Can be used with cordless power tools, but holes will be cut slower

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
DIA-00030	Diamond Drill Bit 6mm	40	84	20	175
DIA-00035	Diamond Drill Bit 8mm	40	84	20	175
DIA-00040	Diamond Drill Bit 10mm	42	84	20	175
DIA-00045	Diamond Drill Bit 12mm	44	84	20	175
DIA-00050	Diamond Drill Bit 14mm	46	84	20	175

Copyright: Linear Tools 2013

Data Sheet: LDS 1451 Date: 19-09-2013

Diamond Drill Bits Page 2 of 2

Diamond Drill Bits with M14 Internal Thread



Large range individual Diamond Drill Bits 22 – 45mm Dry cutting

M14 Internal threads

Cutting speed:

For best results use 2500 – 3000 RPM

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
DIA-00065	Diamond Drill Bit 22mm	95	80	27	152
DIA-00075	Diamond Drill Bit 35mm	227	115	50	185
DIA-00080	Diamond Drill Bit 40mm	262	115	50	185
DIA-00090	Diamond Drill Bit 45mm	280	115	50	185

Copyright: Linear Tools 2013