

8100 SA/SC 2 Zyklop Speed ratchet set, 1/4" drive and 1/2" drive, metric, 43 pieces



The Zyklop Speed Ratchets, 1/4"



EAN/GTIN: 4013288126610
Part no.: 05160785001
Article no.: 8100 SA/SC 2

Dimension: 365x310x70 mm
Weight: 5249 g
Country of origin: CZ
Customs tariff number: 82041200

- Combines five different types of a ratchet in one
- Flywheel design and easy-to-grip free-turning sleeve for very high working speeds
- 43-piece set in a robust metal case
- Fine-pitched teeth for small return angle; switchover ring (right, fixed, left)
- "Take it easy" Tool Finder with colour coding according to sizes

Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_4_the_zyklop_speed_ratchets_1_4_8100_sa_sc_2.html

Wera - 8100 SA/SC 2
05160785001 - 4013288126610

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The Zyklop Speed Ratchets, 1/4"

43-piece Zyklop set in robust metal case: Zyklop ratchet with 1/4" drive and Zyklop ratchet with 1/2" drive. The 72 fine-pitched teeth enable a low return angle of only 5°. The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work conveniently in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking positions at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head. The ratchet can be used as a conventional screwdriver in the 0° position by attaching an adaptor and a bit. The flywheel design ensures rapid screwdriving. The rotation-symmetric construction of the Kraftform handle and the free-turning sleeve support rapid twisting. The outstanding design of the Kraftform handle fits perfectly into the hand preventing hand injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle. The softer anti-slip zones enable the low-loss transfer of high torque. For 1/4" square sockets as well as 1/4" adaptors with square drive, equipped with ball lock. Including 21 Zyklop sockets, 2 Zyklop extensions with free-turning sleeve, 1 Kraftform bit holder with quick-release chuck, 16 bits. "Take it easy" Tool Finder with colour coding according to sizes.

Weblink


http://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_4_the_zyklop_speed_ratchets_1_4_8100_sa_sc_2.html

Wera - 8100 SA/SC 2
05160785001 - 4013288126610


Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The Zyklop Speed Ratchets, 1/4"


Content:

 **8000 A**
05003500001 1 x 1/4"x152.0




 **8790 HMA**
05003501001 1 x 4.0x23.0
05003502001 1 x 4.5x23.0
05003503001 1 x 5.0x23.0
05003504001 1 x 5.5x23.0
05003505001 1 x 6.0x23.0
05003506001 1 x 7.0x23.0
05003507001 1 x 8.0x23.0
05003508001 1 x 9.0x23.0
05003509001 1 x 10.0x23.0
05003511001 1 x 12.0x23.0
05003512001 1 x 13.0x23.0




 **8784 A1**
05003529001 1 x 1/4"x37.0




 **8796 LA**
05003531001 1 x 1/4"x150.0




 **8000 C**
05003600001 1 x 1/2"x277.0




 **8790 HMC**
05003604001 1 x 13.0x37.0
05003605001 1 x 14.0x37.0
05003606001 1 x 15.0x37.0
05003607001 1 x 16.0x37.0
05003608001 1 x 17.0x37.0
05003609001 1 x 18.0x37.0
05003610001 1 x 19.0x37.0
05003612001 1 x 21.0x37.0
05003613001 1 x 22.0x37.0
05003614001 1 x 24.0x37.0




 **8796 LC**
05003643001 1 x 1/2"x250.0




 **816 R**
05051462001 1 x 1/4"x119




 **800/4 Z**
05059488001 1 x 1.0x5.5x89




 **840/4 Z Hex-Plus**
05059630001 1 x 3.0x89
05059631001 1 x 4.0x89
05059632001 1 x 5.0x89
05059633001 1 x 6.0x89




 **851/4 Z PH**
05059760001 1 x PH 1x89
05059775001 1 x PH 2x89
05059795001 1 x PH 3x89



 **855/4 Z PZ**
05060029001 1 x PZ 1x89
05060035001 1 x PZ 2x89
05060043001 1 x PZ 3x89



 **867/4 Z TORX® BO**
05060050001 1 x TX 10x89
05060051001 1 x TX 15x89
05060052001 1 x TX 20x89
05060053001 1 x TX 25x89
05060054001 1 x TX 30x89



Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_4_the_zyklop_speed_ratchets_1_4_8100_sa_sc_2.html

Wera - 8100 SA/SC 2
05160785001 - 4013288126610

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The Zyklop Speed Ratchets, 1/4"

Zyklop "6 in 1"



Incredibly fast 1/4" Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely




The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers




The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

Two-tone foam insert



Perfectly conceived in every detail: the storage case for the Zyklop Speed ratchet sets! The two-tone foam insert section means that the tools can be quickly and reliably replaced, and that missing tools can be detected immediately. The tools and their position can be clearly seen in the lid where they have been laser-etched, ensuring that they are legible even when the insert section is covered with grease, dirt or oil. Additionally, the foam section can be removed and placed in the drawer of a tool cabinet or trolley.

Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_4_the_zyklop_speed_ratchets_1_4_8100_sa_sc_2.html

Wera - 8100 SA/SC 2
05160785001 - 4013288126610

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

8100 SA/SC 2 Zyklop Speed ratchet set, 1/4" drive and 1/2" drive, metric, 43 pieces

The Zyklop Speed Ratchets, 1/4"



Weblink

http://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_4_the_zyklop_speed_ratchets_1_4_8100_sa_sc_2.html

Wera - 8100 SA/SC 2

05160785001 - 4013288126610

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de