

CP1-10B-10



Products → Low Voltage Products and Systems → Control Products → Pilot Devices
→ Pilot Devices - Compact Range

General Information

Extended Product Type:	CP1-10B-10
Product ID:	1SFA619100R1016
EAN:	7320500240762
Catalog Description:	PUSHBUTTON#CP1-10B-10
Long Description:	Compact Pushbutton - Momentary - Flush - Black - Non-illuminated - Black plastic - 1NO

Ordering

EAN:	7320500240762
Minimum Order Quantity:	10 piece
Customs Tariff Number:	8536501999

Dimensions

Product Net Width:	0.030 m
Product Net Height:	0.030 m
Product Net Depth / Length:	0.055 m
Product Net Weight:	0.018 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	0.1 m
Package Level 1 Height:	0.03 m
Package Level 1 Depth / Length:	0.1 m
Package Level 1 Gross Weight:	0.018 kg
Package Level 2 Units:	10

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	-----------------------------------------------------------------

Additional Information

Actuator Type:	Flush
Bezel Material:	Black plastic
Block:	1NO
Color:	Black

Degree of Protection:	Front IP69K Terminals IP20
Function:	Momentary
Illumination:	Non-illuminated
Mechanical Durability:	0.5 million
Number of Auxiliary Contacts NO:	1
Product Main Type:	CP1
Product Name:	Pushbutton
Product Range:	Compact
Product Type:	CP
Rated Frequency (f):	Supply Circuit 60 Hz Supply Circuit 50 Hz
Rated Operational Current AC-15 (I_e):	(24 / 127 V) 1.5 A (220 / 240 V) 1 A
Rated Operational Current DC-13 (I_e):	(24 V) 0.3 A (125 V) 0.2 A
RoHS Date:	0626 5

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SFC151005C0201
Declaration of Conformity - CE:	1SFA1-70
Environmental Information:	1SFC151009D0201
Instructions and Manuals:	1SFC151005C0201
RoHS Information:	1SFC151012D0202

Classifications

E-nummer:	3705389
ETIM 4:	EC002024 - Accessories for control circuit devices
ETIM 5:	EC001028 - Push button, complete
ETIM 6:	EC001028 - Push button, complete
Object Classification Code:	S
UNSPSC:	39121512

