#### **POWER TOOLS & ACCESSORIES**

1-800-386-0191 INFO@TITAN-U5.COM

Drill Bits & Accessories

## 5 pc. Hex Shank Drill Bit Set 16505

- Cobalt Steel bits for wood, plastic & metal
- Use with a bit holder or insert directly into a drill
- Sizes include: 1/16", 3/32", 1/8", 5/32" & 3/16"
- Convenient storage rack



UPC	Master	Inner
8-02090-16505-4	24	6

#### 27 pc. Micro Drill Set with Driver 11003

● 27pc Set Includes: (1) Micro Driver. (2) Dual-End Collets (stored in handle) (24) Drill Bits (2 of each size) #52 (.0635), #54 (.0550) #56 (.0465),



#58 (.0420), #60 (.0400), #62 (.0380) #64 (.0360), #66 (.0330), #68 (.0310), #70 (.0280) #72 (.0250), #74 (.0225)

- Great for a variety of drilling & cleaning uses such as:
- Fuel injectors, carburetor jets, welding & soldering torch tips, water jets, electronics service & repairs

UPC	Master	Inner
8-02090-11003-0	48	6

## 22 pc. Titanium Drill Bit 11006



- Titanium nitride coating extends the life of the bit up to six times longer than standard high speed steel drill bits
- Contains: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 11/64, 3/16, 13/64, 7/32, 15/64, 1/4, 17/64, 9/32, 19/64, 5/16, 21/64, 11/32, 23/64, 3/8"
- Includes plastic storage case

UPC	Master	Inner
8-02090-11006-1	36	6

# 170 pc. Titanium Coated Drill Bit Set 11170

- Titanium coated bits last up to six times longer than a normal bit
- Made of high speed steel for durability
- Includes convenient metal storage case
- 19 different drill bit sizes:
- (5 ea) 21/64, 23/64, 3/8, & 1/2
- (10 ea) 3/64, 1/16, 5/64, 3/32, 1/8, 9/64, 5/32, 11/64, 3/16, 7/32, 15/64, 1/4, 9/32, 19/64, & 5/16"

UPC	Master	Inner
8-02090-11170-9	5	1



# 29 pc. Titanium Coated Drill Bit Set 16530

- Sizes include: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 11/64, 3/16, 13/64, 7/32, 15/64, 1/4, 17/64, 9/32, 19/64, 5/16, 21/64, 11/32, 23/64, 3/8, 25/64, 13/32, 27/64, 7/16, 29/64, 15/32, 31/64 and 1/2 inch
- Reduced shank bits for use with 3/8" chuck
- 118° Standard point tips
- Titanium coating helps resist rust
- Made of high speed steel for added strength & durability
- Convenient storage case

UPC	Master	Inner
8-02090-16530-6	12	6

