

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5054481071](#)
Status: **Active**
Overview: Micro-Lock Plus Wire-to-Board Connector System
Description: Micro-Lock PLUS Right Angle Header, 1.25mm Pitch, Dual Row, Tin-Bismuth Plating, 10 Circuits, Black

Documents:

3D Model	Packaging Specification 5054489200-200 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5054320000-002 (PDF)	Product Literature (PDF)

Agency Certification

UL E29179

General


Product Family	PCB Headers
Series	505448
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Literature Order No	987651-4888
Product Name	Micro-Lock PLUS
UPC	889056765077

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	1183.700/mg
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505448](#) Series

Mates With

Micro-Lock PLUS Receptacle Housing
[505432](#)

Material Info

Reference - Drawing Numbers

Packaging Specification

5054489200-200

Product Specification

5054320000-002

Sales Drawing

5054480000-000, 5054480001-000

This document was generated on 07/31/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION