

# CR-U 91CV



CR-U 91CV Pluggable module varistor and LED green, 110-230VAC/110VDC

## General Information

|                       |                                                                                                                                                                                                                              |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type | CR-U 91CV                                                                                                                                                                                                                    |
| Product ID            | 1SVR405665R1100                                                                                                                                                                                                              |
| EAN                   | 4013614529214                                                                                                                                                                                                                |
| Catalog Description   | CR-U 91CV Pluggable module varistor and LED green, 110-230VAC/110VDC                                                                                                                                                         |
| Long Description      | The CR-U 91CV plug-in module is a pluggable function module for the CR-U range sockets. This module provides overvoltage protection and a green LED indication. The rated control supply voltage is 110-230 V AC / 110 V DC. |

## Ordering

|                        |          |
|------------------------|----------|
| Minimum Order Quantity | 10 piece |
| Customs Tariff Number  | 85389099 |

## Popular Downloads

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 2CDC117008D0204 |
| Instructions and Manuals          | 2CDC117008D0204 |

## Dimensions

|                            |          |
|----------------------------|----------|
| Product Net Width          | 34 mm    |
| Product Net Height         | 24 mm    |
| Product Net Depth / Length | 9 mm     |
| Product Net Weight         | 0.007 kg |

## Technical

|                                                |                                                       |
|------------------------------------------------|-------------------------------------------------------|
| Function                                       | Accessory for interface relays CR-U                   |
| Sub-Function                                   | Pluggable function module for universal relay sockets |
| Sub-Function 2                                 | Overvoltage protection<br>green LED                   |
| Output                                         | none                                                  |
| Output Signal                                  | none                                                  |
| Rated Control Supply Voltage (U <sub>s</sub> ) | 110 V DC<br>110 ... 230 V AC<br>110 ... 230 V AC/DC   |

## Environmental

|             |                                   |
|-------------|-----------------------------------|
| RoHS Status | Following EU Directive 2011/65/EU |
|-------------|-----------------------------------|

## Certificates and Declarations (Document Number)

|                                |                          |
|--------------------------------|--------------------------|
| CSA Certificate                | CSA_262671-2785566       |
| cURus Certificate              | cURus508_E244328         |
| Declaration of Conformity - CE | 1SVD982020-0001          |
| EAC Certificate                | EAC_RU_C-PL.ME77.B.01873 |
| Environmental Information      | 1SAA981009-2401          |
| Instructions and Manuals       | 2CDC117008D0204          |
| RoHS Information               | 1SVD982020-0001          |

## Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | 10 piece      |
| Package Level 1 Width          | 180 mm        |
| Package Level 1 Height         | 220 mm        |
| Package Level 1 Depth / Length | 9 mm          |
| Package Level 1 Gross Weight   | 0.072 kg      |
| Package Level 1 EAN            | 4013614374517 |

## Classifications

|                            |                                            |
|----------------------------|--------------------------------------------|
| Object Classification Code | K                                          |
| E-nummer                   | 4005453                                    |
| ETIM 4                     | EC002586 - Accessories for switching relay |
| ETIM 5                     | EC002586 - Accessories for switching relay |
| ETIM 6                     | EC002586 - Accessories for switching relay |
| ETIM 7                     | EC002586 - Accessories for switching relay |
| eClass                     | 7.0 27379208                               |
| UNSPSC                     | 43172000                                   |

## Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

