

STRIPAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX
Order No.	9005000000
Version	Stripping and cutting tool, Flexible and solid conductors with PVC insulation, 10mm ² , 25mm
GTIN (EAN)	4008190072506
Qty.	1 pc(s).

STRIPAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	190 mm	Width (inches)	7.48 inch
Height	99 mm	Height (inches)	3.898 inch
Depth	22 mm	Depth (inches)	0.866 inch
Weight	225 g	Net weight	222 g

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section (cutting capacity)	6 mm ²
Conductor cross-section, max.	10 mm ²	Conductor cross-section, min.	0.08 mm ²
Conductor cross-section, min. AWG	AWG 28	Stripping length, max.	25 mm
Stripping range, min.	0.08 mm ²		

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC002109
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-90	eClass 7.1	21-04-37-06
eClass 8.1	21-04-37-06	eClass 9.0	21-04-38-90
eClass 9.1	21-04-37-06		

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 8 SAI 15/16 EN
Engineering Data	9005000000_26125_Stripax_6_STP.stp

Data sheet

STRIPAX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

