

Accessories
PS 2.3 RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|----------------------------|
| Type | PS 2.3 RT |
| Order No. | 0180400000 |
| Version | Accessories, Test plug |
| GTIN (EAN) | 4008190060121 |
| Qty. | 20 pc(s). |

Data sheet

Accessories PS 2.3 RT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 5.4 mm | Width (inches) | 0.213 inch |
| Height | 5.4 mm | Height (inches) | 0.213 inch |
| Depth | 32.5 mm | Depth (inches) | 1.28 inch |
| Net weight | 1.21 g | | |

Temperatures

| | | | |
|-----------------------------------|--------|----------------------------------|--------|
| Operating temperature range, max. | 100 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C | | |

Material data

| | | | |
|---------------------------|--------------|--------|-----|
| Material | Polyamide 66 | Colour | Red |
| UL 94 flammability rating | V-2 | | |

System specifications

| | | | |
|---------|-----------|---------------|------|
| Version | Test plug | Mounting rail | none |
|---------|-----------|---------------|------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|---------|
| Installation advice | Direct mounting | Type of fixing | Plugged |
| Type of mounting | Plugged | | |

Conductors for clamping (rated connection)

| | |
|--------------------|--------------------|
| Type of connection | Plug-in connection |
|--------------------|--------------------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC002255 | ETIM 4.0 | EC002255 |
| ETIM 5.0 | EC002255 | ETIM 6.0 | EC002555 |
| UNSPSC | 30-21-18-01 | eClass 6.2 | 27-14-92-14 |
| eClass 7.1 | 27-14-92-14 | eClass 8.1 | 27-14-11-48 |
| eClass 9.0 | 27-14-11-48 | eClass 9.1 | 27-14-11-48 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN CAT 2 PORTFOLIOGUIDE EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | 0180400000_02242_PS_2.3_STP.stp 02242_PS_2.3_RT_DXF.dxf |