

Crimping tool PZ 6 Roto

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 6 Roto
Order No.	9014350000
Version	Crimping tool, Crimping tool for wire-end ferrules, 0.14mm ² , 6mm ² , Trapezoidal crimp
GTIN (EAN)	4008190406615
Qty.	1 pc(s).

Data sheet

**Crimping tool
PZ 6 Roto**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	428 g	Net weight	427.28 g

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, min.	0.14 mm ²
Crimping range, max.	6 mm ²		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, min.	0.14 mm ²
Wire end ferrules cross-section, max.	6 mm ²		


Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-10
eClass 8.1	21-04-38-10	eClass 9.0	21-04-38-10
eClass 9.1	21-04-38-11		

Product information

Descriptive text ordering data	Additional accessories can be found in Chapter J
Descriptive text accessories	Information and ordering data for wire end ferrules - see chapter J accessories wire end ferrules

Approvals

Approvals	
ROHS	Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD

Data sheet

**Crimping tool
PZ 6 Roto**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

