

**Crimping tool  
MTR 35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts.**

- Comprehensive range of standard-compliant crimp inserts
- Wide choice of mechanical, hydraulic and electro-hydraulic tools
- large processing range up to 300 mm<sup>2</sup>
- Release option in the event of incorrect operation

**General ordering data**

Type	MTR 35
Order No.	<a href="#">9017500000</a>
Version	Crimping tool, Crimping tool, universal hand presses, 6mm <sup>2</sup> , 50mm <sup>2</sup>
GTIN (EAN)	4008190042417
Qty.	1 pc(s).

**Crimping tool  
MTR 35**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	270 mm	Width (inches)	10.63 inch
Weight	1.3 kg	Net weight	1,497 g

**Technical data**

Version	Mechanical, with interchangeable inserts
---------	--

**Description of contact**

Type of contact	Tubular cable lug, rolled connector	Crimping range, min.	6 mm <sup>2</sup>
Crimping range, max.	50 mm <sup>2</sup>		

**tool data crimping**

Copper connector (rolled), min.	6 mm <sup>2</sup>	Copper connector (rolled), max.	35 mm <sup>2</sup>
Insulated connectors, min.	10 mm <sup>2</sup>	Insulated connectors, max.	25 mm <sup>2</sup>
Wire end ferrules cross-section, min.	25 mm <sup>2</sup>	Wire end ferrules cross-section, max.	50 mm <sup>2</sup>
Deviation	8 mm		

**Classifications**

ETIM 3.0	EC001282	ETIM 4.0	EC001282
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Product information**

Descriptive text technical data	For more details see crimp inserts on the following pages
Descriptive text accessories	Crimping inserts see on the following pages

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
--------------------	--------------------------------------

**Data sheet**

**Crimping tool  
MTR 35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

