

**Industrial Ethernet
IE-FCM-USB-A**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Service interface FrontCom[®] Micro with USB in IP65

General ordering data

Type	IE-FCM-USB-A
Order No.	1018840000
Version	FrontCom Micro USB coupling, USB 2.0, Type A
GTIN (EAN)	4032248730094
Qty.	10 pc(s).

**Industrial Ethernet
IE-FCM-USB-A**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Wall thickness, max.	3 mm	Wall thickness, min.	1 mm
Net weight	2.3 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

General Info

Connection 1	USB A	Connection 2	USB A
Description of article	FrontCom Micro USB coupling, USB 2.0	Wiring	Type A
Colour	Black	Housing main material	PA UL 94 V0
Type of mounting	Cabinet, Distribution box	Shielding	360° shield contact
Protection degree	IP67, in closed state	Plugging cycles	≥ 1500

Standards

Connector standard	IEC 61076-3-107	Certificate no. (cULus)	E316369
--------------------	-----------------	-------------------------	---------

Downloads

UL Approval	DUXR.E316369.pdf
-------------	------------------

Classifications

ETIM 3.0	EC000674	ETIM 4.0	EC000674
ETIM 5.0	EC000674	ETIM 6.0	EC001121
eClass 5.1	27-25-05-04	eClass 6.2	27-25-05-04
eClass 7.1	27-25-05-04	eClass 8.1	19-17-01-25
eClass 9.0	19-17-01-25	eClass 9.1	27-18-90-90

Product information

Descriptive text technical data	Approvals available on request
---------------------------------	--------------------------------

Approvals


Approvals



ROHS	Conform
------	---------

**Industrial Ethernet
IE-FCM-USB-A**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Dimensioned drawing****Installation cut-out**