

TEC 1050

... the power to perform

POWER
ADHESIVES


CORDLESS CARTRIDGE GLUE GUN

The **TEC 1050** is an advanced electronic cordless glue gun for dispensing **TECBOND** 'CT' 50g adhesive cartridges. It comes complete with a combined stand and heating station.

This tool is used for dispensing polyurethane reactive hotmelts (PURs), plus peelable and full pressure sensitive hotmelt adhesives that cannot be used through normal glue guns.

The tool is easily loaded with **TECBOND** CT cartridges. These take 10-15 minutes to heat through, and the warning light on the heating station turns green to indicate the tool is ready.

There is no waste, as the CT cartridges come complete with a built-in ball check valve nozzle and a screw on cap. Like normal hotmelts, the adhesive can be simply re-melted the next time the tool is switched on.



ADVANCED FEATURES



Cordless applicator



Base heating station with red 'on' light and green 'ready' indicator



Ball check valve incorporated in each glue cartridge plus nozzle cap eliminates waste



Quick and easy glue cartridge re-load

SPECIFICATION

VOLTAGE	230V or 110-120V 50-60HZ
HEATER	PTC heater 14 watt (500 watt warm up)
TEMP CONTROL	Self-regulating heater
WEIGHT	Heating station 260g, Gun 250g
POWER CABLE	Gun is cordless, heating station 2m cable fitted with UK, Euro or US plug
MELT RATE	Approximately 1 x 50g cartridge every 10 minutes
ADHESIVE	TECBOND 50g CT cartridge (PURs & Pressure sensitive hotmelts)

The **TEC 1050** brings another dimension to handheld hotmelt glue gun applications. Capable of dispensing high performance PURs such as **TECBOND 9010CT**. This type of adhesive combines structural performance with the convenience of a hotmelt and is capable of bonding substrates such as wood, ceramics, leather, metal textiles and some plastic etc, with much improved heat and chemical resistance over conventional hotmelt.



The **TEC1050** gun is also capable of dispensing full pressure sensitive and peelable hot melts. This means we can now offer glues with an indefinite open time, and also glues that can be peeled off for temporary bonding (such as fixing give-away promotional articles onto magazines etc).



ADHESIVE RE-ORDER

TECBOND 9010-CT HIGH PERFORMANCE POLYURETHANE REACTIVE HOTMELT (PUR) GRADE

TECBOND 2169-CT MULTI-PURPOSE PEELABLE PRESSURE SENSITIVE HOTMELT

TECBOND 4741-CT MULTI-PURPOSE VERY AGGRESSIVE PERMANENTLY TACKY PRESSURE SENSITIVE HOTMELT

