



### 55NCG All-Purpose Pliers



- All-purpose pliers
- Oval head
- Standard beveled edges
- Forged alloy steel construction, precision machining and scientific proportioning
- Exceptional strength and performance
- Red plastic-coated cushion grip provides maximum leverage

| Catalog Number | UPC Number   | Packed | Length (inch) | Length (mm) | A (inch) | A (mm) | B (inch) | B (mm) | C (inch) | C (mm) | E (inch) | E (mm) | Pack weight (lb) | Pack weight (g) | Shelf pack |
|----------------|--------------|--------|---------------|-------------|----------|--------|----------|--------|----------|--------|----------|--------|------------------|-----------------|------------|
| 55NCG          | 037103213297 | Boxed  | 5             | 125         | 3/4      | 19     | 19/32    | 15     | 3/8      | 10     | -        | -      | 22.2             | 629             | 6          |
| 55NCGV         | 037103213327 | Carded | 5             | 125         | 3/4      | 19     | 19/32    | 15     | 3/8      | 10     | -        | -      | 22.2             | 629             | 6          |


### 64CG Semi-flush Tip Cutting Pliers



- For use in close quarters and semi-flush tip cutting of fine wires
- Forged alloy steel construction, precision machining and scientific proportioning
- Exceptional strength and performance
- Red plastic-coated cushion grip provides maximum leverage
- Tapered jaw

| Catalog Number | UPC Number   | Packed | Length (inch) | Length (mm) | A (inch) | A (mm) | B (inch) | B (mm) | C (inch) | C (mm) | E (inch) | E (mm) | Pack weight (lb) | Pack weight (g) | Shelf pack |
|----------------|--------------|--------|---------------|-------------|----------|--------|----------|--------|----------|--------|----------|--------|------------------|-----------------|------------|
| 64CGV          | 037103481764 | Carded | 4             | 100         | 13/32    | 10     | 7/16     | 11     | 9/32     | 7      | 1/32     | 0.8    | 12.5             | 354             | 6          |

### 66NCG All-Purpose Pliers



- All-purpose pliers
- Oval head
- Standard beveled edges
- Forged alloy steel construction, precision machining and scientific proportioning
- Exceptional strength and performance
- Red plastic-coated cushion grip provides maximum leverage

| Catalog Number | UPC Number   | Packed | Length (inch) | Length (mm) | A (inch) | A (mm) | B (inch) | B (mm) | C (inch) | C (mm) | E (inch) | E (mm) | Pack weight (lb) | Pack weight (g) | Shelf pack |
|----------------|--------------|--------|---------------|-------------|----------|--------|----------|--------|----------|--------|----------|--------|------------------|-----------------|------------|
| 66NCG          | 037103213457 | Boxed  | 6             | 152         | 27/32    | 21     | 11/16    | 17     | 7/16     | 11     | -        | -      | 42.2             | 1196            | 6          |
| 66NCGV         | 037103213464 | Carded | 6             | 152         | 27/32    | 21     | 11/16    | 17     | 7/16     | 11     | -        | -      | 42.2             | 1196            | 6          |