

Brand Name:	Acer
DVI:	Yes
Environmentally Friendly:	Yes
Form Factor:	Desktop
Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of USB 2.0 Ports:	4
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-7400
Processor Speed:	3 GHz
Processor Type:	Core i5
Product Family:	Veriton X2640G
Product Type:	All-in-One Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	500 GB
Total Number of USB Ports:	8
VGA:	Yes

### Display & Graphics

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
TV Card:	No

### General Information

Brand Name:	Acer
Manufacturer Part Number:	DT.VPUEK.022
Manufacturer Website Address:	<a href="http://www.acer.co.uk">http://www.acer.co.uk</a>
Manufacturer:	Acer, Inc
Product Line:	Veriton
Product Name:	Veriton X2640G All-in-One Computer
Product Series:	X2640G
Product Type:	All-in-One Computer

### I/O Expansions

Number of PCI Express x1 Slots:	1
Number of PCI Express x16 Slots:	1
Number of Total Expansion Slots:	2

### Input Devices

Keyboard Type:	Physical Keyboard
Keyboard:	Yes
Pointing Device Type:	Mouse

### Interfaces/Ports

Audio Line In:	Yes
Audio Line Out:	Yes
DVI:	Yes
Modem (RJ-11):	No
Network (RJ-45):	Yes
Number of USB 2.0 Ports:	4
Number of USB 3.1 Gen 1 Ports:	4
Total Number of USB Ports:	8
VGA:	Yes

### Memory

Maximum Memory:	32 GB
Memory Card Reader:	No
Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none"><li>• DMI</li><li>• GS</li><li>• PC2001</li><li>• Citrix ready</li><li>• BSMI</li><li>• VCCI</li><li>• CE</li><li>• FCC</li><li>• CB</li></ul>
Environmental Certification:	EPEAT Silver RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none"><li>• Veriton X2640G All-in-One Computer</li><li>• USB Keyboard</li><li>• USB Mouse</li></ul>

## Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

## Physical Characteristics

Depth:	354 mm
Form Factor:	Desktop
Height:	265 mm
Width:	100 mm

## Power Description

Maximum Power Supply Wattage:	220 W
----------------------------------	-------

## Processor & Chipset

64-bit Processing:	Yes
Cache:	6 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Direct Media Interface:	8 GT/s
Maximum Turbo Speed:	3.50 GHz
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Quad-core (4 Core)
Processor Generation:	7th Gen
Processor Manufacturer:	Intel
Processor Model:	i5-7400
Processor Speed:	3 GHz
Processor Type:	Core i5

## Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

## Storage

Hard Drive Configuration:	1 x 500 GB
Hard Drive Interface:	Serial ATA
Hard Drive RPM:	5400
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD±R/±RW
Total Hard Drive Capacity:	500 GB