

Straight SMA Bulkhead Jack, Solder



Specifications

Connector Body Style : Straight Bulkhead Jack
 Coaxial Termination : Solder
 Connector Mounting : Cable
 Coaxial Cable Types : RG-402

Electrical Specifications

Frequency Range : DC 26.5GHz
 Nominal Impedance : 50Ω
 Voltage Rating : 500V Max.
 VSWR : 1.16 Max. @ 18GHz
 1.2 Max. @ 26.5GHz

Material Specifications

Bodies : Stainless Steel per JIS SUS 303
 Centre Contact : Beryllium Copper per ASTM B196 UNS C17300
 Insulation : PTFE per ASTM D1457 and ASTM D1710


Mechanical Specifications

Interface in accordance with : MIL-STD-348A
 Cable Attachment : Outer: Solder; Inner: Solder

Environmental Specification

Operating Temperature : -65°C to +165°C

Diagram



Dimensions : Millimetres (Inches)

No.	Description	Material	Finish
1	Nut	Stainless Steel	Gold 3μ" Min.
2	Washer	Stainless Steel	Gold 3μ" Min.
3	O-Ring	Silicone	Black
4	Body	Stainless Steel	Gold 10μ" Min.
5	Insulation	PTFE	-
6	Centre Contact	Beryllium Copper	Gold 50μ" Min.

www.element14.com
 www.farnell.com
 www.newark.com



Straight SMA Bulkhead Jack, Solder

Part Number Table

Description	Part Number
Straight SMA Bulkhead Jack, Solder, 50Ω, RG-402	MC002924

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com

