

1569 ESD Nutdriver, 4.0 x 60 mm

ESD Series



EAN:	4013288184115	Size:	157x13x13 mm
Part number:	05030417001	Weight:	19 g
Article number:	1569 ESD	Country of origin:	CZ
		Customs tariff number:	82054000



- Kraftform Micro screwdriver for hexagon head screws
- ESD-safe tool thanks to surface resistance of $< 10^9 \text{ Ohm}$
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Hexagonal anti-roll feature against rolling away
- Chrome-plated

ESD-safe Micro screwdriver. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work.

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_screwdrivers_esd_series_1569_esd.html

Wera - 1569 ESD
05030417001 - 4013288184115

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

ESD Series

Wera ESD Tools

High protection

Kraftform Micro Handle

The precision zone




The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.




Multi-component screwdriver handle for ergonomic working.



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone

Rotating cap and fast-turning zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.






Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_screwdrivers_esd_series_1569_esd.html

Wera - 1569 ESD
05030417001 - 4013288184115

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

		 mm	 mm	 mm	 inch
05030410001	1.5	60	97	5.7	2 3/8
05030411001	1.8	60	97	5.7	2 3/8
05030412001	2.0	60	97	5.7	2 3/8
05030413001	2.5	60	97	5.7	2 3/8
05030414001	3.0	60	97	5.7	2 3/8
05030415001	3.2	60	97	5.7	2 3/8
05030416001	3.5	60	97	5.7	2 3/8
05030417001	4.0	60	97	5.7	2 3/8
05030418001	4.5	60	97	6.4	2 3/8
05030150001	5.0	60	97	7.0	2 3/8
05030151001	5.5	60	97	7.8	2 3/8

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_screwdrivers_esd_series_1569_esd.html

Wera - 1569 ESD

05030417001 - 4013288184115

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de