## 8740 A HF Zyklop bit socket with 1/4" drive with holding function, 7,0 x 28 mm

#### Innovations and Autumn/Winter Campaign 2017/2018













EAN: 4013288189547

Article number:

Part number: 05003341001

8740 A HF

Weight:

Country of origin:

**Customs tariff** 

number:

Size:

82079030

20 g

CZ

95x44x20 mm

- · Hex-Plus allows socket head screws to live longer
- Take it easy tool finder with colour coding according to sizes
- The holding function holds screws securely on the tool
- Knurling on lower end for more grip when used manually
- Bit socket (non-impact) for manual or machine tool operations

Bit socket with 1/4 inch drive and holding function for extremely convenient screwdriving with reduced risk of losing the screw when addressing the workpiece. "Take it easy" Tool Finder with colour coding according to size - for simple and rapid accessing of the required tool.

#### Innovations and Autumn/Winter Campaign 2017/2018



# Bit sockets with retaining function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

# Bit sockets with retaining function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

#### **Hex-Plus**



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

#### Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

#### Innovations and Autumn/Winter Campaign 2017/2018



#### Manual and machine sockets

#### Zyklop Accessories





The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

We did not just want our creativity to end with the ratchets themselves so we also occupied ourselves intensively with ratchet accessories. That is why our users are now provided with an extension with freely spinning sleeve and flexible lock to enable more secure and more rapid screwdriving. The sockets have been completely redesigned: we wanted to spare the user the need of having two different series one for manual and the other for power tool applications. And: we wanted to enormous simplify the task of finding the right sizes. Technically, our own ambitious goals represented a real challenge: to endow sockets with the advantage of the holding function on screwdrivers and bits. We succeeded in this!

# 8740 A HF Zyklop bit socket with 1/4" drive with holding function, 7,0 x 28 mm

## Innovations and Autumn/Winter Campaign 2017/2018



### Further versions in this product family:

		0	0				*
		mm	inch	mm	mm	mm	mm
05003332001	leuchtpink	3.0		28.0	12.0	12.5	11.0
05003333001	gelb	4.0	,	28.0	12.0	12.5	11.0
05003334001	gelb	4.0	•	100.0	12.0	12.5	83.0
05003335001	leuchtorange	5.0		28.0	12.0	12.5	11.0
05003336001	leuchtorange	5.0	•	100.0	12.0	12.5	83.0
05003337001	rot	6.0		28.0	12.0	12.5	11.0
05003338001	rot	6.0		100.0	12.0	12.5	83.0
05003341001	violett	7.0		28.0	12.0	12.5	11.0
05003342001	violett	7.0	•	100.0	12.0	12.5	83.0
05003339001	pink	8.0		28.0	12.0	12.5	11.0
05003340001	pink	8.0	•	100.0	12.0	12.5	83.0
05003383001	leuchtpink		1/8	28.0	12.0	12.5	11.0
05003384001	weiss		9/64	28.0	12.0	12.5	11.0
05003385001	gelb		5/32"	28.0	12.0	12.5	11.0
05003386001	leuchtorange		3/16"	28.0	12.0	12.5	11.0
05003387001	rot		7/32"	28.0	12.0	12.5	11.0
05003388001	tuerkis		1/4"	28.0	12.0	12.5	11.0
05003389001	pink		5/16"	28.0	12.0	12.5	11.0