

The Zyklop Ratchets, 3/8"



|                        |               |                               |               |
|------------------------|---------------|-------------------------------|---------------|
| <b>EAN:</b>            | 4013288121165 | <b>Size:</b>                  | 285x240x55 mm |
| <b>Part number:</b>    | 05003596001   | <b>Weight:</b>                | 3149 g        |
| <b>Article number:</b> | 8100 SB 4     | <b>Country of origin:</b>     | CZ            |
|                        |               | <b>Customs tariff number:</b> | 82041100      |

- Combines five different types of a ratchet in one
- Flywheel design and easy-to-grip free-turning sleeve for very high working speeds
- 38-piece set in a robust metal case
- Freely pivoting ratchet head
- Take it easy tool finder with colour coding according to sizes

38-piece Zyklop set in robust metal case: Zyklop ratchet with 3/8" drive. The 72 fine-pitched teeth enable a low return angle of only 5°. The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work conveniently in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking positions at 0°, 15° und 90°, both to the right and left, ensure safe working without any slipping of the ratchet head. The ratchet can be used as a conventional screwdriver in the 0° position by attaching an adaptor and a bit. The flywheel design ensures rapid screwdriving. The rotation-symmetric construction of the Kraftform handle and the free-turning sleeve support rapid twisting. The outstanding design of the Kraftform handle fits perfectly into the hand preventing hand injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle. The softer anti-slip zones enable the low-loss transfer of high torque. For 3/8" square sockets as well as 3/8" adaptors with square drive, equipped with ball lock. Including 12 imperial Zyklop sockets, 2 Zyklop extensions with free-turning sleeve, 1 T-handle, 1 wobble extension, 1 universal joint, 1 adaptor with quick-release chuck, 19 bits. "Take it easy" Tool Finder with colour coding according to sizes.

**Web link**

[http://products.wera.de/en/tools\\_for\\_the\\_aerospace\\_segment\\_ratchets\\_the\\_zyklop\\_ratchets\\_3\\_8\\_8100\\_sb\\_4.html](http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklop_ratchets_3_8_8100_sb_4.html)

Wera - 8100 SB 4  
05003596001 - 4013288121165

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

# 8100 SB 4 Zyklop Speed ratchet set, 3/8" drive, imperial, 38 pieces



## The Zyklop Ratchets, 3/8"

### Set contents:



**8000 B**  
05003550001 1 x 3/8"x199.0




**8790 HMB**  
05003569001 1 x 1/4"x29.0  
05003570001 1 x 5/16"x29.0  
05003571001 1 x 11/32"x29.0  
05003572001 1 x 3/8"x29.0  
05003573001 1 x 7/16"x29.0  
05003574001 1 x 1/2"x29.0  
05003575001 1 x 9/16"x29.0  
05003576001 1 x 5/8"x30.0  
05003577001 1 x 11/16"x30.0  
05003578001 1 x 3/4"x30.0  
05003579001 1 x 13/16"x30.0  
05003580001 1 x 7/8"x30.0



**8789 B**  
05003581001 1 x 3/8"x165.0



**8794 B**  
05003584001 1 x 3/8"x76.0



**8795 B**  
05003585001 1 x 3/8"x50.0



**8784 B1**  
05003590001 1 x 1/4"x3/8"x44.0



**8796 SB**  
05003591001 1 x 3/8"x125.0



**8796 LB**  
05003592001 1 x 3/8"x200.0



**851/1 Z PH**  
05072072001 1 x PH 2x25  
05072074001 1 x PH 3x25



**855/1 Z PZ**  
05072082001 1 x PZ 2x25  
05072084001 1 x PZ 3x25



**867/1 Z TORX® B0**  
05066500001 1 x TX 10x25  
05066505001 1 x TX 15x25  
05066510001 1 x TX 20x25  
05066515001 1 x TX 25x25  
05066520001 1 x TX 27x25  
05066525001 1 x TX 30x25  
05066530001 1 x TX 40x25



**800/1 Z**  
05072059001 1 x 1.0x5.5x25



**840/1 Z Hex-Plus**  
05135069001 1 x 9/64x25  
05135071001 1 x 5/64x25  
05135072001 1 x 3/32x25  
05135073001 1 x 1/8x25  
05135074001 1 x 5/32"x25  
05135075001 1 x 3/16"x25  
05135079001 1 x 7/32"x25

### Web link

[http://products.wera.de/en/tools\\_for\\_the\\_aerospace\\_segment\\_ratchets\\_the\\_zyklop\\_ratchets\\_3\\_8\\_8100\\_sb\\_4.html](http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklop_ratchets_3_8_8100_sb_4.html)

Wera - 8100 SB 4  
05003596001 - 4013288121165

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## The Zyklop Ratchets, 3/8"

### The Zyklop Speed Ratchet



Incredibly fast 1/4" Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



The Wera Zyklop Speed ratchet combines the advantages of five different types of ratchet in one. And it is a really fast mover.

### Pivots freely



The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

### Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

### Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

### Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

### Screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

### Two-tone foam insert



Perfectly conceived in every detail: the storage case for the Zyklop Speed ratchet sets! The two-tone foam insert section means that the tools can be quickly and reliably replaced, and that missing tools can be detected immediately. The tools and their position can be clearly seen in the lid where they have been laser-etched, ensuring that they are legible even when the insert section is covered with grease, dirt or oil. Additionally, the foam section can be removed and placed in the drawer of a tool cabinet or trolley.

### Web link

[http://products.wera.de/en/tools\\_for\\_the\\_aerospace\\_segment\\_ratchets\\_the\\_zyklop\\_ratchets\\_3\\_8\\_8100\\_sb\\_4.html](http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklop_ratchets_3_8_8100_sb_4.html)

Wera - 8100 SB 4  
05003596001 - 4013288121165

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

8100 SB 4 Zyklop Speed ratchet set, 3/8" drive, imperial, 38 pieces

The Zyklop Ratchets, 3/8"



**Web link**

[http://products.wera.de/en/tools\\_for\\_the\\_aerospace\\_segment\\_ratchets\\_the\\_zyklop\\_ratchets\\_3\\_8\\_8100\\_sb\\_4.html](http://products.wera.de/en/tools_for_the_aerospace_segment_ratchets_the_zyklop_ratchets_3_8_8100_sb_4.html)

Wera - 8100 SB 4

05003596001 - 4013288121165

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)