

7450 Kraftform ESD pre-set adjustable torque screwdrivers with Rapidaptor quick-release chuck, 1/4 inch, 0,1 - 0,34 Nm  
Series 7400 Kraftform Torque Screwdrivers



<b>EAN:</b>	4013288179210	<b>Size:</b>	170x40x40 mm
<b>Part number:</b>	05074820001	<b>Weight:</b>	122 g
<b>Article number:</b>	7400 vor ESD	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000



- Pre-set Kraftform ESD torque screwdriver
- ESD-safe tool thanks to surface resistance of  $< 10^9$  Ohm
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Suitable for bits with 1/4" hex head drive
- Rapidaptor quick-release chuck for bits with 1/4" hex head drive

Wera torque screwdriver. Secure protection against electrostatic charge and associated damage. Comes with pre-set torque value for all applications where the same, constant torque and repeat accuracy are required. The torque value can be modified within a specific measurement range. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

**Web link**

[http://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_pre-set\\_adjustable\\_torque\\_models\\_7400\\_vor\\_esd.html](http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_pre-set_adjustable_torque_models_7400_vor_esd.html)

Wera - 7400 vor ESD  
05074820001 - 4013288179210

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Wera ESD Tools**



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

**High protection**



The electric surface resistance of the Wera ESD material is  $\leq 10^9$  ohm. This securely protects components against electrostatic energy and associated damage.

**Pre-set, adjustable Torque Screwdrivers**



These tools are ideal for all applications where a constant, identical torque is required and where a high degree of repeat accuracy is needed. The torque value can be adjusted within the measuring range.

**Versatile**



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

**Rapid-in and self-lock**



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

**Rapid-out**




Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

**Chuck-all**



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

**Single-hand function**



Every function of the Rapidaptor quick-release chuck, such as inserting or releasing bits, can be carried out with one hand. This is faster, more economical and more ergonomic. There are no unnecessary manoeuvres.

**Web link**

[http://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraffform\\_torque\\_screwdrivers\\_pre-set\\_adjustable\\_torque\\_models\\_7400\\_vor\\_esd.html](http://products.wera.de/en/torque_tools_series_7400_kraffform_torque_screwdrivers_pre-set_adjustable_torque_models_7400_vor_esd.html)







Wera - 7400 vor ESD  
05074820001 - 4013288179210

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**7450 Kraftform ESD pre-set adjustable torque screwdrivers with Rapidaptor quick-release chuck, 1/4 inch, 0,1 - 0,34 Nm**  
**Series 7400 Kraftform Torque Screwdrivers**



Further versions in this product family:

								
	art. no.	mm	inch	nm	nm	mm	inch	
	<b>05074820001</b>	<b>7450 ESD</b>	<b>89</b>	<b>1/4</b>	<b>0.1</b>	<b>0.1-0.34</b>	<b>133</b>	<b>5 1/4</b>
	05074820010 <sup>1)</sup>	7450 ESD	89	1/4	0.1	0.1-0.34	133	5 1/4
	05074822001	7451 ESD	89	1/4	0.3	0.3-1.0	133	5 1/4
	05074822010 <sup>1)</sup>	7451 ESD	89	1/4	0.3	0.3-1.0	133	5 1/4
	05074824001	7452 ESD	89	1/4	0.9	0.9-1.5	133	5 1/4
	05074824010 <sup>1)</sup>	7452 ESD	89	1/4	0.9	0.9-1.5	133	5 1/4
	05074840001	7460 ESD	105	1/4	0.3	0.3-1.2	155	6
	05074840010 <sup>1)</sup>	7460 ESD	105	1/4	0.3	0.3-1.2	133	6
	05074842001	7461 ESD	105	1/4	1.2	1.2-3.0	155	6
	05074842010 <sup>1)</sup>	7461 ESD	105	1/4	1.2	1.2-3.0	155	6

1) Other pre-set values within the adjustable range can be delivered on request

**Web link**

[http://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_pre-set\\_adjustable\\_torque\\_models\\_7400\\_vor\\_esd.html](http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_pre-set_adjustable_torque_models_7400_vor_esd.html)

Wera - 7400 vor ESD  
 05074820001 - 4013288179210

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de