

7460 Krafftform pre-set adjustable torque screwdrivers with Rapidaptor quick-release chuck, 1/4 inch, 0,3 Nm  
Series 7400 Krafftform Torque Screwdrivers



<b>EAN:</b>	4013288102911	<b>Size:</b>	155x37x37 mm
<b>Part number:</b>	05074715001	<b>Weight:</b>	180 g
<b>Article number:</b>	7400 vor	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000



- Adjustable Krafftform torque screwdriver with Rapidaptor quick-release chuck
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached
- Multi-component Krafftform handle for high working speeds

Wera torque screwdriver. Pre-set torque value for all applications where the same, constant torque and repeat accuracy are required. The torque value can be modified within a specific measurement range. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Krafftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

**Web link**

[http://products.wera.de/en/torque\\_tools\\_series\\_7400\\_krafftform\\_torque\\_screwdrivers\\_pre-set\\_adjustable\\_torque\\_models\\_7400\\_vor.html](http://products.wera.de/en/torque_tools_series_7400_krafftform_torque_screwdrivers_pre-set_adjustable_torque_models_7400_vor.html)

Wera - 7400 vor  
05074715001 - 4013288102911


Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Pre-set, adjustable torque screwdrivers**



Pre-set torque, adjustable within a defined range. Also available in ESD version (also for HIOS/Halfmoon bits) and with Krafftform Micro handle.

**Unlimited torque**



Unlimited torque for loosening seized screws.

**Versatile**



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

**Rapid-in and self-lock**




The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

**Rapid-out**



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

**Chuck-all**



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

**Single-hand function**



Every function of the Rapidaptor quick-release chuck, such as inserting or releasing bits, can be carried out with one hand. This is faster, more economical and more ergonomic. There are no unnecessary manoeuvres.

**Web link**

[http://products.wera.de/en/torque\\_tools\\_series\\_7400\\_krafftform\\_torque\\_screwdrivers\\_pre-set\\_adjustable\\_torque\\_models\\_7400\\_vor.html](http://products.wera.de/en/torque_tools_series_7400_krafftform_torque_screwdrivers_pre-set_adjustable_torque_models_7400_vor.html)







Wera - 7400 vor  
05074715001 - 4013288102911

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

**7460 Kraftform pre-set adjustable torque screwdrivers with Rapidaptor quick-release chuck, 1/4 inch, 0,3 Nm**  
**Series 7400 Kraftform Torque Screwdrivers**



Further versions in this product family:

								
	art. no.	mm	inch	nm	nm	mm	inch	
	05074790001	7450	89	1/4	0.1	0.1-0.34	133	5 1/4
	05074790010 <sup>1)</sup>	7450	89	1/4	0.1	0.1-0.34	133	5 1/4
	05074792001	7451	89	1/4	0.3	0.3-1.0	133	5 1/4
	05074792010 <sup>1)</sup>	7451	89	1/4	0.3	0.3-1.0	133	5 1/4
	05074794001	7452	89	1/4	0.9	0.9-1.5	133	5 1/4
	05074794010 <sup>1)</sup>	7452	89	1/4	0.9	0.9-1.5	133	5 1/4
	<b>05074715001</b>	<b>7460</b>	<b>105</b>	<b>1/4</b>	<b>0.3</b>	<b>0.3-1.2</b>	<b>155</b>	<b>6</b>
	05074715010 <sup>1)</sup>	7460	105	1/4	0.3	0.3-1.2	155	6
	05074716001	7461	105	1/4	1.2	1.2-3.0	155	6
	05074716010 <sup>1)</sup>	7461	105	1/4	1.2	1.2-3.0	155	6
	05133177001	7464	105	1/4	3.3	3.0-6.0	155	6

<sup>1)</sup> Other pre-set values within the adjustable range can be delivered on request

**Web link**

[http://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_pre-set\\_adjustable\\_torque\\_models\\_7400\\_vor.html](http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_pre-set_adjustable_torque_models_7400_vor.html)

Wera - 7400 vor  
 05074715001 - 4013288102911

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de