

# 00 21 02 EL

## Tool Bag "Electric"



- Light design made of hard-wearing, reinforced polyester fabric
- Front additionally reinforced with aluminium brackets
- Semi-fold-out front with adjustable loops and exterior document compartment
- With galvanized steel base tray
- With carrying handle and adjustable shoulder strap
- Dimensions, interior (W x H x D): 420 x 250 x 160 mm
- Contains 23 brand name quality tools, partly VDE tested according to DIN EN/IEC 60900

|                     |               |
|---------------------|---------------|
| <b>Article No.</b>  | 00 21 02 EL   |
| <b>EAN</b>          | 4003773081951 |
| <b>Net weight g</b> | 6700          |

technical change and errors excepted

### Content 00 21 02 EL (23)

| Article No. |              |   | Quantity | Nominal size |  |
|-------------|--------------|---|----------|--------------|--|
| 03 06 180   | Knipex       | Combination Pliers                                      | 1        | 180 mm       |  |
| 11 06 160   | Knipex       | Insulation Stripper                                     | 1        | 160 mm       |  |
| 25 06 160   | Knipex       | Snipe Nose Side Cutting Pliers, Radio Pliers            | 1        | 160 mm       |  |
| 70 06 160   | Knipex       | Diagonal Cutter   | 1        | 160 mm       |  |
| 98 52       | Knipex       | Cable Knife   | 1        | 185 mm       |  |
| 16 95 01 SB | Knipex       | KNIPEX ErgoStrip®, Universal Stripping Tool             | 1        |              |  |
| 306125      | Haunstätter  | PUK® Junior Hacksaw                                     | 1        | 150 x 240 mm |  |
| 3185-04     | maurerfreund | Painter's spatula, wood, high quality                   | 1        | 40 mm        |  |
| 30490-800   | Picard       | Chipping hammer   | 1        | 800 g        |  |
| 3003010119  | Picard       | Locksmith's hammer                                      | 1        | 300 g        |  |
| 71510-000   | Picard       | Metre ruler (yardstick)                                 | 1        | 2 m          |  |
| 75040-015   | Picard       | Flat brush  | 1        | 40 mm        |  |
| 75063-000   | Picard       | Plaster bowl  | 1        | 127 x 94     |  |
| 340 300 1   | Rennsteig    | Mason's Chisels   | 1        |              |  |
| 361 252 1   | Rennsteig    | Electrician's Chisel                                    | 1        | 250 x 10 mm  |  |
| 98 20 25    | Knipex       | Screwdrivers for slotted screws                         | 1        | 2,5 mm       |  |
| 98 20 35 SL | Knipex       | Screwdriver (Slim) for slotted screws                   | 1        | 3,5 x 100 mm |  |
| 98 20 55 SL | Knipex       | Screwdriver (Slim) for slotted screws                   | 1        | 5,5 mm       |  |
| 98 20 65 SL | Knipex       | Screwdriver (Slim) for slotted screws                   | 1        | 6,5 mm       |  |
| 98 24 01 SL | Knipex       | Screwdriver (Slim) for cross-recessed screws, Phillips® | 1        | PH1          |  |
| 98 24 02 SL | Knipex       | Screwdriver (Slim) for cross-recessed screws, Phillips® | 1        | PH2          |  |
| 465608      | Wera         | Voltage detector, single-pole                           | 1        |              |  |
| 16 20 165   | Knipex       | Dismantling Tool  | 1        | 165 mm       |  |

### Accessories

|                    |            |  |
|--------------------|------------|--|
| <b>Article No.</b> | <b>EAN</b> |  |
|--------------------|------------|--|

00 21 99 V05

4003773082088

Shoulder strap for tool bags and tool cases