

Folding Hex-Key Sets

Hex-Key Sets

- Two key positions (straight-out or right angle) for extra leverage
- Hex ends are square-cut for a secure full-depth fit and maximum contact with the hex socket to prevent slippage and stripping of the socket
- Handy sets fit in your pocket or tool box easily and help eliminate the lost key problem
- Made in the U.S.A.

**Improved
Strength**



70579

Cat. No.	Description	Size	Handle Length	Key Lengths	Color	Weight
70591	Nine-Key Inch Folding Hex Key Set	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"	4-3/8" (111.1 mm)	2-11/16" to 3-13/16" (68.3 to 96.8 mm)	Silver	0.50 lb (0.23 kg)
70581	Eight-Key Inch Folding Hex Key Set	1/20", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32"	3-1/16" (77.8 mm)	1-7/8" to 3" (47.6 to 76.2 mm)	Silver	0.20 lb (0.09 kg)
70579	Five-Key Inch Folding Hex Key Set	3/16", 7/32", 1/4", 5/16", 3/8"	5-3/8" (136.5 mm)	2-11/16" to 3-13/16" (68.3 to 96.8 mm)	Silver	0.85 lb (0.39 kg)
70582	Seven-Key Metric Folding Hex Key Set	1-1/2 mm, 2 mm, 2-1/2 mm, 3 mm, 4 mm, 5 mm, 6 mm	3-45/64" (94 mm)	19/32" to 1-25/32" (15 to 45 mm)	Silver	0.27 lb (0.12 kg)
70580	Six-Key Metric Folding Hex Key Set	3 mm, 4 mm, 5 mm, 6 mm, 8 mm, 10 mm	5-3/8" (136.5 mm)	2-3/8" to 4" (60 to 101 mm)	Silver	0.85 lb (0.39 kg)

Grip-It™ Hex-Key Sets

- Blades rotate independently up to 270°
- Precision fit so hex tool end reduces stripping problems. Keys are industrial strength, impact-resistant and tested for performance to below freezing
- Glass-reinforced nylon handle
- Hex ends are square-cut for a secure full-depth fit and maximum contact with the hex socket to prevent slippage and stripping of the socket (Cat. Nos. 70570, 70573, 70574, and 70575)
- Ball design allows for a thicker neck diameter increasing torque capacity, while maintaining operational angles to 25% (Cat. Nos. 70571 and 70572)
- Made in the U.S.A.



70570

Cat. No.	Description	Size	Handle Length	Key Lengths	Color	Weight
70570	Grip-It® Five Key Hex Set - Inch	3/16", 7/32", 1/4", 5/16", 3/8"	4-7/16" (112.7 mm)	1-37/64" to 1-31/32" (40.1 to 50.0 mm)	Yellow	0.58 lb (0.26 kg)
70571	Grip-It® Five Key Ball Hex Set - Inch	3/16", 7/32", 1/4", 5/16", 3/8"	4-7/16" (112.7 mm)	1-35/64" to 2" (39.3 mm to 50.8 mm)	Yellow	0.58 lb (0.26 kg)
70572	Grip-It® Five Key Ball Hex Set - Metric	5 mm, 6 mm, 7 mm, 8 mm, 10 mm	4-7/16" (112.7 mm)	1-19/32" to 1-15/16" (40.5 to 49.2 mm)	Red	0.58 lb (0.26 kg)
70573	Grip-It® 12 Key Hex Set - Inch/Metric	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	4-7/16" (112.7 mm)	1-7/16" to 2-17/64" (36.5 to 57.6 mm)	Blue	0.30 lb (0.14 kg)
70574	Grip-It® Nine Key Hex Set 2 Positions	5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4"	4-7/16" (112.7 mm)	1-3/4" to 2-17/64" (44.5 to 57.6 mm)	Yellow	0.33 lb (0.15 kg)
70575	Grip-It® Nine Key Hex Set Square Cut	3/64", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16"	3-13/16" (96.8 mm)	1-25/64" to 1-27/32" (35.3 to 46.8 mm)	Yellow	0.20 lb (0.09 kg)

TORX® Sets

Folding TORX® Set

- TORX® drive cuts slippage, saves fasteners, efficiently transmits more torque to the work
- Keys are tough, heat-treated chrome-nickel alloy steel for strength and durability
- Keys fold flat into handle
- Can be used straight out or at an angle for extra leverage

Cat. No.	Size	Handle Length	Key Lengths	Color	Weight
70586	T10, T15, T20, T25, T27, T30, T40	4-3/8" (111.1 mm)	2-13/16" to 3" (71.4 to 76.2 mm)	Silver	0.30 lb (0.14 kg)

TORX® is a trademark of Acument Intellectual Properties, LLC.



70586

