



Equinox analytical balances bring remarkable precision to labs that perform highly detailed testing. The Equinox is ideal for research and quality assurance facilities; science education; precision counting; and production and manufacturing applications needing exceptionally precise results. A color touch screen display provides intuitive operation, with icon-driven menus and readily accessible applications and functions.

Versatile and resilient, Equinox provides intuitive operation and readily accessible functions



## Features

- Large, responsive 5" 800x480 pixel touch-screen display
- Level indicator and adjustable feet ensure proper balance setup for optimum weighing results
- Security slot for optional Kensington-type lock and cable to help prevent theft
- Large, grade 304 stainless steel pan allows easy cleaning
- RS-232 interface is available to provide speedy connection to computers and printers
- USB host for memory card
- Built-in memory for storing products and settings
- External calibration allows for verification and adjustment with weights
- Selectable digital filtering helps minimise effects of vibration and disturbances
- Security password control prevents unauthorised access
- Printouts include date and time for data tracking within Good Laboratory Practices (GLP) guidelines
- Preset tare function speeds the process of repetitive weighing
- Parts counting with freely selectable sample sizes
- Multilingual display allows use in many different countries
- Memory accumulation totals results
- Checkweighing with audible alarm
- AC adapter included

## Applications

- Weighing
- Parts counting
- Percentage weighing
- Checkweighing
- Dynamic / animal weighing
- Accumulation of weight
- Density determination
- Display hold
- Formulation
- Statistics
- Textile

## About ADAM:

For more than 40 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	EAB 125i	EAB 225i	EAB 124e	EAB 224e	EAB 314e	EAB 124i	EAB 224i	EAB 314i	EAB 414i	EAB 514i
<b>Capacity</b>	62g / 120g	82g / 220g	120g	220g	310g	120g	220g	310g	410g	510g
<b>Readability</b>	0.01mg/ 0.1mg	0.01mg/ 0.1mg	0.0001g	0.0001g	0.0001g	0.0001g	0.0001g	0.0001g	0.0001g	0.0001g
<b>Repeatability (S.D.)</b>	0.02mg/ 0.1mg	0.02mg/ 0.1mg	0.0002g	0.0002g	0.0002g	0.0002g	0.0002g	0.0002g	0.0002g	0.0002g
<b>Linearity (+/-)</b>	0.1mg / 0.2mg	0.1mg / 0.2mg	0.0003g	0.0003g	0.0003g	0.0003g	0.0003g	0.0003g	0.0003g	0.0003g
<b>Pan Size</b>	80mm ø									
<b>Weighing Units</b>	g, mg, ct, GN, lb, oz, dwt, mm, ozt, tl.H, tl.S, tl.T, T, custom unit									
<b>Stabilisation Time (sec)</b>	6					4				
<b>Interface</b>	RS-232, USB									
<b>Calibration</b>	Internal automatic calibration			External calibration			Internal automatic calibration			
<b>Display</b>	5" Touchscreen									
<b>Power Supply</b>	24V 50/60Hz 500mA adapter									
<b>Operating Temperature</b>	10° to 30°C									
<b>Housing</b>	ABS plastic									
<b>Draught Shield</b>	Chamber 192x195x230mm									
<b>Overall Dim.</b>	224x374x338mm (wxdxh)									
<b>Net Weight</b>	7.2kg									

## Accessories

### Item number Description

104008036	.....Anti-vibration table
1060014262	.....Density kit
3012014259	.....In-use cover
1120011156	.....ATP thermal printer
3126011263	.....ATP thermal printer paper
3126011281	.....ATP thermal printer paper (pack of 10)
3014011014	.....RS-232 cable M-F
700100046	.....Kensington-type lock and cable
600002028	.....AdamDU Data Collection
700660290	.....Calibration certificate
700100410	.....ABI-1 Ioniser
700100398	.....E1 5g Calibration Weight
700100399	.....E1 10g Calibration Weight
700100400	.....E1 20g Calibration Weight
700100401	.....E1 50g Calibration Weight
700100022	.....E2 100g Calibration Weight
700100023	.....E2 200g Calibration Weight
700100419	.....E1 1mg - 50g Calibration Weight Set
700100420	.....E1 1mg - 100g Calibration Weight Set
700100421	.....E1 1mg - 200g Calibration Weight Set
700100026	.....E2 1mg - 200g Calibration Weight Set
700100207	.....E2 1g to 200g Calibration Weight Set

## Key Accessories



### ATP thermal printer

Easy-to-use features combined with quick set-up equals a truly versatile thermal printer. A single push-button feed key and three easy-to-read LED indicators make operation simple.



### AdamDU data collection program

Adam DU software connects a balance to the laboratory network, helping to achieve seamless data collection, transfer and analysis. DU features an easy-to-use interface with a main command window, allowing users to quickly collect information from up to eight Adam balances simultaneously using RS-232 or USB connections.

## Supplied by