

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **2451361005**
Status: **Active**
Overview: Mega-Fit Power Connectors
Description: Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 0.5m Length, Gold (Au) Plated, 10 Circuits, Black

Documents:

Drawing (PDF) RoHS Certificate of Compliance (PDF)
Packaging Specification 2027040021-PK (PDF) Product Literature (PDF)

General

| | |
|-----------------------------|----------------------------------|
| Product Family | Cable Assemblies |
| Series | <u>245136</u> |
| Application | Power, Wire-to-Board |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Mega-Fit-to-Mega-Fit |
| Overmolded | Yes |
| Overview | <u>Mega-Fit Power Connectors</u> |
| Product Literature Order No | 987651-4662 |
| Product Name | Mega-Fit OTS |
| UPC | 191128799065 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 0.50m |
| Circuits (Loaded) | 10 |
| Color - Resin | Black |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Matte Tin |
| Material - Resin | PBT |
| Net Weight | 205.900/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 5.70mm |
| Plating min - Mating | 0.381µm |
| Plating min - Termination | 0.381µm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 15.50mm |
| Wire Size AWG | 12 |
| Wire/Cable Type | UL 2464 |

Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 16.0A |
| Voltage - Maximum | 300V AC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|----------------|
| Packaging Specification | 2027040021-PK |
| Sales Drawing | 2014400081-000 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

245136 Series

Mates With

Mega-Fit Header 76825 , 76829 , 172064 , 172065