


4mm Banana Plug - Plug Stackable Patchcord - 2.5mm² PVC



Specifications

Lead Length	: 250mm/9.9" 500mm/19.7" 1m / 3.3ft 2m / 6.6ft
Connector Type A	: Stacking 4mm Banana Plug
Connector Type B	: Stacking 4mm Banana Plug
Voltage Rating	: ≤33V AC/≤70V DC
Current Rating	: 36A
Resistance	: 250mm: 12mΩ 500mm: 15mΩ 1m: 20mΩ 2m: 30mΩ
Cable	: 2.5mm ² , PVC
Contact Material	: Brass and Beryllium Copper, Nickel Plated / Gold Nickel Plated
Insulator Material	: Polyamide and Polypropylene
Insulator Colour	: White, Blue, Brown, Grey, Yellow, Yellow/Green, Black, Red, Green and Purple
Temperature	: -20°C to +80°C

Application

General purpose electric and electronic testing, controlling and measuring.

Part Number Table

Description	Insulator Colour	Lead Length	Part Number
Test Lead, Stacking 4mm Banana Plug to Plug, 2.5mm ² PVC, 33V AC/70V DC, 36A	Blue	500mm	72-13880
	Yellow		72-13882
	Black		72-13884
	Red		72-13886
	Green		72-13888
	White	1m	72-13804
	Blue		72-13806
	Yellow		72-13808



4mm Banana Plug - Plug Stackable Patchcord - 2.5mm² PVC



Description	Insulator Colour	Lead Length	Part Number
Test Lead, Stacking 4mm Banana Plug to Plug, 2.5mm ² PVC, 33V AC/70V DC, 36A	Black	1m	72-13810
	Red		72-13812
	Green		72-13814
	Purple		72-13816
	Blue	2m	72-13838
	Yellow		72-13840
	Black		72-13842
	Red		72-13844
	Green		72-13846
	Test Lead, Stacking 4mm Banana Plug to Plug, Gold Contact, 2.5mm ² PVC, 33V AC/70V DC, 36A		White
Blue		72-13850	
Grey		72-13852	
Yellow		72-13854	
Black		72-13856	
Red		72-13858	
Green		72-13860	
White		500mm	72-13862
Blue			72-13864
Brown			72-13866
Grey			72-13868
Yellow			72-13870
Black			72-13872
Red			72-13874
Green			72-13876
Purple			72-13878
White			1m
Blue		72-13786	
Brown		72-13788	
Grey		72-13790	
Yellow		72-13792	
Yellow/Green		72-13794	
Black		72-13796	
Red		72-13798	
Green		72-13800	
Purple		72-13802	
White		2m	72-13818
Blue			72-13820
Brown			72-13822



4mm Banana Plug - Plug Stackable Patchcord - 2.5mm² PVC



Description	Insulator Colour	Lead Length	Part Number
Test Lead, Stacking 4mm Banana Plug to Plug, Gold Contact, 2.5mm ² PVC, 33V AC/70V DC, 36A	Grey	2m	72-13824
	Yellow		72-13826
	Yellow/Green		72-13828
	Black		72-13830
	Red		72-13832
	Green		72-13834
	Purple		72-13836

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

