

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190390016](#)
Status: **Active**
Overview: [Snap Plugs and Receptacles](#)
Description: Avikrimp Snap Plug Receptacle for 14-16 AWG Wire, Nylon, Fits Male Plug Diameter 3.96mm, Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E152602

General

Product Family Quick Disconnects
Series [19039](#)
Comments Fits Male Plug Dia. 3.96mm
Crimp Quality Equipment Yes
Insulated Fully
Overview [Snap Plugs and Receptacles](#)
Product Name Avikrimp
Type Snap Receptacle
UPC 800753049512

Physical

Barrel Type Closed
Color - Resin Blue
Flammability 94V-2
Gender Female
Glow-Wire Capable No
Insulation Nylon (PA)
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.229/g
Orientation Straight
Packaging Type Adhesive Tape on Reel
Plating min - Mating 4.064µm
Plating min - Termination 4.064µm
Tab Thickness N/A
Tab Width N/A
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 3.81mm max.
Wire Size AWG 14, 16
Wire Size mm² 1.00-2.50

Electrical


Voltage - Maximum 600V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number BRB-8156NT



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Missing Compliance Data
RoHS Phthalates	Not Contained

Search Parts in this Series

[19039](#) Series

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-19902-011-001, PS-19902-015-001
SD-19039-001

This document was generated on 09/10/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION