


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191310002**  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** InsulKrimp Block Spade Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Length 27.31mm

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-011-001 (PDF)</a>
<a href="#">Product Specification 194130096-000 (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-009-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

CSA	LR18689
UL	E32244

**General**

Product Family	Ring and Spade Terminals
Series	<u>19131</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>Solderless Terminals</u>
Product Name	InsulKrimp
Type	Spade Block
UPC	800753101258

**Physical**

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	1.782/g
Packaging Type	Bag
Stud Size	10 (M5)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.40mm max.
Wire Size AWG	10, 12
Wire Size mm <sup>2</sup>	3.30-5.00

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	C-2105-10X
--------------------	------------

**Reference - Drawing Numbers**

Product Specification	194130096-000, PS-19902-009-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing	CCD20301

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

**China ROHS**

ELV

Prop65

PropRisk

PropRisk

PropRisk

PropSub

RoHS Phthalates

**Green Image**

Not Relevant

Missing Compliance Data

Cancer

Developmental toxicity

Reproductive toxicity

DEHP

Not Contained

**Search Parts in this Series**

19131 Series