

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349128081](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Header, Right-Angle, SMT, Single Row, 8 Circuits, Tin (Sn) Plating, Polarization Option B, Gray, Tape and Reel

Documents:

3D Model	Packaging Specification PK-31302-213-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-34791-020-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-31301-786 (PDF)	

General

Product Family	PCB Headers
Series	34912
Application	Power, Signal, Wire-to-Board
Overview	Mini50 Connection Systems
Product Literature Order No	987650-5442
Product Name	Mini50
UPC	887191297415

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	Polyester Alloy
Net Weight	2.166/g
Number of Rows	1
Orientation	Right Angle
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-31301-786, PK-31302-213-001
Product Specification	PS-34791-020-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[34912 Series](#)

Mates With

[34791](#) Mini50 Unsealed Single Row
Receptacle

This document was generated on 10/22/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION