

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0367831201](#)
Status: **Active**
Overview: [MX120G Sealed Connectors](#)
Description: MX120G Sealed Header Connector Assembly, 12 Circuit, Color Mark Identification Black

Documents:

[3D Model](#) [Product Specification PS-36783-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series [36783](#)
 Application Wire-to-Board
 Overview [MX120G Sealed Connectors](#)
 Product Name MX120G
 UPC 887191147673

Physical

(p)ower-(s)ignal Configuration 12p - 0s
 Breakaway No
 Circuits (Loaded) 12
 Circuits (maximum) 12
 Color - Resin Black
 Durability (mating cycles max) 10
 First Mate / Last Break No
 Flammability 94HB
 Glow-Wire Capable No
 Guide to Mating Part No
 Lock to Mating Part Yes
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 8.357/g
 Number of Rows 2
 Orientation Right Angle
 PC Tail Length 3.20mm
 PCB Thickness - Recommended 1.60mm
 Packaging Type Carton
 Pitch - Mating Interface 3.20mm
 Pitch - Termination Interface 3.50mm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Robotic Placement None
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40° to +105°C
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 10.5A
 Voltage - Maximum 28V DC

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[36783](#) Series

Mates With

[36792-1201](#) 3.20mm MX120G Pitch Sealed
 Female Connector Assembly

Lead-freeProcess Capability

WAVE

Material Info

Reference - Drawing Numbers

Product Specification

PS-36783-001-001

Sales Drawing

SD-36783-004-001

This document was generated on 09/14/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION