


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0039000073**
Status: **Active**
Overview: Mini-Fit Jr. Power Connectors
Description: Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel

Documents:

Drawing (PDF)	Product Specification TS-5556-002-001 (PDF)
Product Specification PS-5556-001-001 (PDF)	Packaging Specification PK-5556-001-001 (PDF)
Product Specification PS-5556-002-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	<u>5556</u>
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>Mini-Fit Jr. Power Connectors</u>
Packaging Alternative	<u>39-00-0074 (Loose)</u>
Product Name	Mini-Fit
UPC	800753825178

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	5556GS4
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001-001
Product Specification	PS-5556-001-001, PS-5556-002-001, TS-5556-002-001
Sales Drawing	SD-5556-006-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

5556 Series

Mates With

5558 Mini-Fit Crimp Male Terminals. 5559 Plug Housing. Mini-Fit Jr. Header, Dual Row, 5566 , 5569

Use With

5557 Mini-Fit Jr. Receptacle Housing